



Build ID: 1216
Date: 2025-04-09

IPC1752A Materials Compliance Declaration

Sections	A,D
Response Document	1216
Mode	Distribute
Response Date	4/9/2025 6:43:35 AM

Company Name TE Connectivity

Contact Name TE Product Compliance

Contact Title TE Product Compliance

Contact Phone +001-800-522-6752

Contact Email productcompliance@te.com

Products

Item Number	Item Name	Qty	Effective Date	Manufacturing Site	Mass	Unit of Measure	Version	SCIP PSSI #
206060-1	CPC PLUG ASSEMBLY SIZE 11-4	0	2025-04-09		16.027980000000	g		
.....704790-2 1	Nylon Compound	0	2025-04-09		4.000000000000	g		
.....704790-2 2	Nylon Compound	0	2025-04-09		4.000000000000	g		
....704790-4 7	Nylon Compound	2	2025-04-09		6.000000000000	g		
....704790-4 8	Nylon Compound	3	2025-04-09		6.000000000000	g		
..213811-1	COUPLING RING,SZ 11,CPC	1	2025-04-09		6.313980000000	g		
..207000-1	PLUG FOR SOC CONT, SZ 11-4 CPC	1	2025-04-09		9.714000000000	g		
.....704790-1 3	Nylon Compound	1	2025-04-09		4.000000000000	g		



Build ID: 1216
Date: 2025-04-09

.....704790-1 4	Nylon Compound	1	2025-04-09	4.000000000000	g
.....704790-1 5	Nylon Compound	0	2025-04-09	4.000000000000	g
.....704790-1 6	Nylon Compound	0	2025-04-09	4.000000000000	g



Build ID: 1216
Date: 2025-04-09

Article Categories

Item Number	Article Category Id	Article Category Text
-------------	---------------------	-----------------------

Query List Statements

Authority	Identity	Statement	Response
IPC	EUROHS-1907	Product(s) does not meet EU RoHS requirements and is not under exemptions	False
IPC	EUROHS-1907	Product(s) is obsolete, no information is available	False
IPC	EUROHS-1907	Product(s) is unknown, no information is available	False
IPC	EUROHS-1907	Product(s) meets EU RoHS requirements by application of the selected exemption(s)	False
IPC	EUROHS-1907	Product(s) meets EU RoHS requirements without any exemptions	False



Build ID: 1216
Date: 2025-04-09

Declaration

Standard

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form.



Build ID: 1216
Date: 2025-04-09

Full Material Disclosure

Product	Qty	Material Name / Material Category	Material %	Material Mass	Substance Name	Substance Percentage	Substance Identity	Substance Authority	Mass	Unit of Measure	Exemption
Nylon Compound704790-1 3	1										
		704790-1	100.00000000000000	100.00000000000000mg							
					Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	2.40000000000000	101357-15-7	CAS	24.00000000000000	mg	
					CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	3.60000000000000			36.00000000000000	mg	
					Phosphorous	11.00000000000000	7723-14-0	CAS	110.00000000000000	mg	
					Fibrous-Glass-Wool	25.00000000000000	65997-17-3	CAS	250.00000000000000	mg	
					Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	58.00000000000000	32131-17-2	CAS	580.00000000000000	mg	
Nylon Compound704790-1 4	1										
		704790-1	100.00000000000000	100.00000000000000mg							



Build ID: 1216

Date: 2025-04-09

					Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	2.400000000000	101357-15-7	CAS	24.000000000000	mg	
					CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	3.600000000000			36.000000000000	mg	
					Phosphorous	11.000000000000	7723-14-0	CAS	110.000000000000	mg	
					Fibrous-Glass-Wool	25.000000000000	65997-17-3	CAS	250.000000000000	mg	
					Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	58.000000000000	32131-17-2	CAS	580.000000000000	mg	
Nylon Compound704790-1 5	0										
		704790-1	100.000000000000	100.000000000000mg							
					Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	2.400000000000	101357-15-7	CAS	24.000000000000	mg	
					CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	3.600000000000			36.000000000000	mg	
					Phosphorous	11.000000000000	7723-14-0	CAS	110.000000000000	mg	
					Fibrous-Glass-Wool	25.000000000000	65997-17-3	CAS	250.000000000000	mg	
					Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	58.000000000000	32131-17-2	CAS	580.000000000000	mg	



Build ID: 1216
Date: 2025-04-09

Nylon Compound704 790-1 6	0										
		704790-1	100.0 0000 0000 000	100.000000000000mg							
					Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	2.400000 000000	101357-1 5-7	CAS	24.00000000 0000	mg	
					CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	3.600000 000000			36.00000000 0000	mg	
					Phosphorous	11.000000 0000000	7723-14-0	CAS	110.0000000 00000	mg	
					Fibrous-Glass-Wool	25.000000 0000000	65997-17- 3	CAS	250.0000000 00000	mg	
					Poly[imino(1,6- dioxo-1,6- hexanediyl)]imino-1,6- hexanediyl]	58.000000 0000000	32131-17- 2	CAS	580.0000000 00000	mg	