



Build ID: 1288
Date: 2025-04-10

IPC1752A Materials Compliance Declaration

<i>Sections</i>	<i>A,D</i>
<i>Response Document</i>	<i>1288</i>
<i>Mode</i>	<i>Distribute</i>
<i>Response Date</i>	<i>4/10/2025 3:21:34 AM</i>

Company Name TE Connectivity

Contact Name TE Product Compliance

Contact Title TE Product Compliance

Contact Phone +001-800-522-6752

Contact Email productcompliance@te.com

Products

Item Number	Item Name	Qty	Effective Date	Manufacturing Site	Mass	Unit of Measure	Version	SCIP PSSI #
1-1676480-6	CRG0402 1% 160K	0	2025-04-10		0.000533000000	g		



Build ID: 1288
Date: 2025-04-10

Article Categories

Item Number	Article Category Id	Article Category Text
-------------	---------------------	-----------------------

Query List Statements

Authority	Identity	Statement	Response
IPC	EUROHS-1907	Product(s) does not meet EU RoHS requirements and is not under exemptions	False
IPC	EUROHS-1907	Product(s) is obsolete, no information is available	False
IPC	EUROHS-1907	Product(s) is unknown, no information is available	False
IPC	EUROHS-1907	Product(s) meets EU RoHS requirements by application of the selected exemption(s)	False
IPC	EUROHS-1907	Product(s) meets EU RoHS requirements without any exemptions	False



Build ID: 1288
Date: 2025-04-10

Declaration

Standard

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form.



Build ID: 1288
Date: 2025-04-10

Full Material Disclosure

Product	Qty	Material Name / Material Category	Material %	Material Mass	Substance Name	Substance Percentage	Substance Identity	Substance Authority	Mass	Unit of Measure	Exemption
CRG0402 1% 160K1-16764 80-6	0										
		Termination inner C3	0.013140000000	0.013140000000mg							
					Chromium	19.999714248975	7440-47-3	CAS	0.000013998000	mg	
					Nickel	80.000285751025	7440-02-0	CAS	0.000055993000	mg	
		Protective coating G1	0.566960000000	0.566960000000mg							
					Ethyl cellulose	2.999997682095	9004-57-3	CAS	0.000090599000	mg	
					3-Cyclohexene-1-methanol, .alpha.,.alpha.,4-trimethyl-, (1S)-	30.000009933877	10482-56-1	CAS	0.000905991000	mg	
					Frits, chemicals (lead bisilicate)	66.999992384028	65997-18-4	CAS	0.002023379000	mg	
		Resistive element	0.600750000000	0.600750000000mg							
					Lead oxide (lead monoxide)	0.167908558743	1317-36-8	CAS	0.000005373000	mg	7(c)-I



Build ID: 1288

Date: 2025-04-10

				Ruthenium dioxide	5.000006 250086	12036-10-1	CAS	0.000159998 000	mg	
				Palladium	10.00001 2500172	7440-05-3	CAS	0.000319996 000	mg	
				Silver	25.00000 0000000	7440-22-4	CAS	0.000799989 000	mg	
				Frits, chemicals (lead bisilicate)	59.83207 2691000	65997-18-4	CAS	0.001914600 000	mg	
		Protective coating G2	1.096 1900 0000 0	1.096190000000mg						
				Talc	5.340003 692435	14807-96-6	CAS	0.000311801 000	mg	
				Copper Chromite black spinel	13.32999 7126204	68186-91-4	CAS	0.000778334 000	mg	
				Silica, Vitreous	33.32999 3700940	60676-86-0	CAS	0.001946127 000	mg	
				(CHLOROMETHYL)OXIRANE, 4,4'-(1-METHYLETHYLIDENE)BISPHENOL COPOLYMER	48.00000 5480422	25068-38-6	CAS	0.002802704 000	mg	
		Termination inner C2	1.244 6900 0000 0	1.244690000000mg						
				Frits, chemicals (lead bisilicate)	13.04000 6540003	65997-18-4	CAS	0.000864548 000	mg	
				Silver	86.95999 3459997	7440-22-4	CAS	0.005765418 000	mg	
		Termination inner C1	2.209 6600 0000 0	2.209660000000mg						



Build ID: 1288

Date: 2025-04-10

					Frits, chemicals (lead bisilicate)	4.350000 743417	65997-18-4	CAS	0.000511994 000	mg	
					Silver	95.64999 9256583	7440-22-4	CAS	0.011257981 000	mg	
		Termination outer	6.578 3000 0000 0	6.578300000000mg							
					Tin	100.0000 00000000	7440-31-5	CAS	0.035039973 000	mg	
		Termination between	6.683 4300 0000 0	6.683430000000mg							
					Nickel	100.0000 00000000	7440-02-0	CAS	0.035599958 000	mg	
		Substrate	81.00 6640 0000 00	81.006640000000mg							
					Magnesium oxide	1.999999 916568	1309-48-4	CAS	0.008629799 000	mg	
					Quartz (SiO2)	1.999999 916568	14808-60-7	CAS	0.008629799 000	mg	
					Aluminium Oxide	96.00000 0166864	1344-28-1	CAS	0.414230370 000	mg	