



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	485203835	Response Date	2013-09-12	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1761987-1	Amount	1250.309742	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1761988-1				1.0	629.1594	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	629.1594	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	18.87478	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	421.5368	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	188.74782	mg	
Sub-Item	1	1761989-2				13.0	17.825723	mg	
Material	2	Nickel Plate				13.0	0.65484	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	13.0	0.00130968	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	6.5484E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.65288	mg	
Material	2	Gold Plate				13.0	0.053865	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.0537034	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	13.0	1.616E-4	mg	
Material	2	Tin Plate				13.0	0.141818	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	13.0	1.4168E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	13.0	0.14168	mg	
Material	2	Phos Bronze				13.0	16.9752	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.0169752	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.00169752	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	13.0	0.0339504	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	13.0	0.00254628	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0335	13.0	15.28337	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	13.0	0.00339504	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	13.0	0.0594132	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	1.6975E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	13.0	0.0169752	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.00169752	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	13.0	1.52777	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	13.0	0.0169752	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	8.4876E-5	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	13.0	0.00169752	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.0084876	mg	
Sub-Item	1	1761990-2				13.0	23.316811	mg	
Material	2	Nickel Plate				13.0	0.857504	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	13.0	0.00171501	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	8.575E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.85493	mg	
Material	2	Gold Plate				13.0	0.053865	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.05370341	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	13.0	1.616E-4	mg	
Material	2	Tin Plate				13.0	0.176642	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	13.0	1.7647E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	13.0	0.17647	mg	
Material	2	Phos Bronze				13.0	22.2288	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.0222288	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.00222288	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	13.0	0.0444576	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	13.0	0.00333432	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0335	13.0	20.01337	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	13.0	0.00444576	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	13.0	0.0778008	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	2.2229E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	13.0	0.0222288	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.00222288	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	13.0	2.00059	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	13.0	0.0222288	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	1.1114E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	13.0	0.00222288	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.0111144	mg	
Sub-Item	1	1888064-1				1.0	86.2974	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	86.2974	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	2.58892	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	57.81926	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	25.88922	mg	