



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Kim, Seong Kyung	Contact Title	Channel Sales Manager		
Company Unique ID	-	Response Date	2013-07-15	Contact Email	sophie.kim@te.com				
Contact Phone Number	+82-2-3415-4614								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1954097-1	Amount	592.36	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1954098-2				1.0	233.1	mg	
Material	2	LCP-TD30				1.0	233.1	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	32.0	1.0	74.592	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	68.0	1.0	158.508	mg	
Sub-Item	1	1954099-1				2.0	179.63	mg	
Material	2	Phos Bronze				2.0	175.5	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	2.0	166.16954	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0351	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.01755	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	2.0	7.8975	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	2.0	0.026325	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.1755	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.01755	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.001755	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	2.0	0.5265	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	2.0	0.1755	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.1755	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.01755	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.08775	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.1755	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	8.775E-4	mg	
Material	2	Tin Plate				2.0	2.73	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	2.0	0.00272727	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	2.0	2.72727	mg	
Material	2	Nickel Plate				2.0	1.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	0.0028	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.0014	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	1.3958	mg	