



TE Materials Compliance Declaration

Sections	A,D
Response Document	520
Mode	Distribute
Response Date	3/25/2025 11:54:57 PM

Build ID: 520
Date: 2025-03-26

Company Name	TE Connectivity
Contact Name	TE Product Compliance
Contact Title	TE Product Compliance
Contact Phone	+001-800-522-6752
Contact Email	productcompliance@te.com

Products

Item Number	Item Name	Qty	Effective Date	Manufacturing Site	Mass	Total Mass	Unit of Measure	Version	SCIP PSSI #
5145274-1	CONN SEC II 13 POS 100C/L	1.0000 00000	2025-03-25		19.628432 000000	19.6284320 00	g		
..145279-1	STD EDGE II HSG 100 CL 13 POS	1.0000 00000	2025-03-25		4.3990000 00000	4.39900000 0	g		
.....5-703377-1 1	Base Metals	0.0730 00000	2025-03-25		4.0000000 00000	0.29200000 0	g		
.....5-703377-1 2	Base Metals	0.0730 00000	2025-03-25		4.0000000 00000	0.29200000 0	g		
....9-646054-0 3	CONTACT, STD EDGE II, .100 CL	1.0000 00000	2025-03-25		1.1714948 40000	1.17149484 0	g		
....9-646054-0 4	CONTACT, STD EDGE II, .100 CL	1.0000 00000	2025-03-25		1.1714948 40000	1.17149484 0	g		
..9-646054-8	STD EDGE II STRP PLTD 100CL	13.000 00000	2025-03-25		0.5857474 20000	7.61471646 0	g		



		0				
..9-646054-1	CONTACT, STD EDGE II, .100 CL	13.000 00000	2025-03-25	0.5857474 20000	7.61471646 0	g
		0				
.....646054-9 5	STD EDGE II CONTACT 100 CL	1.0000 00000	2025-03-25	0.5840000 00000	0.58400000 0	g
.....646054-9 6	STD EDGE II CONTACT 100 CL	1.0000 00000	2025-03-25	0.5840000 00000	0.58400000 0	g
.....TEC-100-221A00 13	Base Metals	1.0000 00000	2025-03-25	2.0000000 00000	2.00000000 0	g
.....TEC-100-221A00 14	Base Metals	1.0000 00000	2025-03-25	2.0000000 00000	2.00000000 0	g
.....2288478-3 7	112-25-3, PLATING, NICKEL, ELEC TRODEPOSIT	0.0000 42110	2025-03-25	2.0000000 00000	0.00008422 0	g
.....2288478-3 8	112-25-3, PLATING, NICKEL, ELEC TRODEPOSIT	0.0000 42110	2025-03-25	2.0000000 00000	0.00008422 0	g
.....2288474-1 9	TEC-112-65-1, PLATING, TIN (LEAD-FREE)	0.0007 63000	2025-03-25	2.0000000 00000	0.00152600 0	g
.....2288474-1 10	TEC-112-65-1, PLATING, TIN (LEAD-FREE)	0.0007 63000	2025-03-25	2.0000000 00000	0.00152600 0	g
.....2288504-5 11	112-162-5, PLATING, GOLD, ELECTRODEPOSIT	0.0000 68600	2025-03-25	2.0000000 00000	0.00013720 0	g
.....2288504-5 12	112-162-5, PLATING, GOLD, ELECTRODEPOSIT	0.0000 68600	2025-03-25	2.0000000 00000	0.00013720 0	g
....1573755-1	Polyester Compound	4.3990 00000	2025-03-25	1.0000000 00000	4.39900000 0	g



Article Categories

Item Number	Article Category Id	Article Category Text
-------------	---------------------	-----------------------

Query List Statements

Authority	Identity	Statement	Response
IPC	EUROHS-1907	Product(s) does not meet EU RoHS requirements and is not under exemptions	False
IPC	EUROHS-1907	Product(s) is obsolete, no information is available	False
IPC	EUROHS-1907	Product(s) is unknown, no information is available	False
IPC	EUROHS-1907	Product(s) meets EU RoHS requirements by application of the selected exemption(s)	False
IPC	EUROHS-1907	Product(s) meets EU RoHS requirements without any exemptions	True



Declaration

Standard

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.



Full Material Disclosure

Product	Qty	Material Name / Material Category	Material %	Material Mass	Material Unit of Measure	Substance Name	Substance Percentage	Substance Identity	Substance Authority	Mass	Unit of Measure	Exemption
Base Metals TEC-10 0-221A00 13	1.00000000	100-221	100.000000000000	1000.000000000000	mg							
						Mercury	0.000500000000	7439-97-6	CAS	0.005000000000	mg	
						Beryllium	0.001000000000	7440-41-7	CAS	0.010000000000	mg	
						Arsenic	0.005000000000	7440-38-2	CAS	0.050000000000	mg	
						Cadmium	0.005000000000	7440-43-9	CAS	0.050000000000	mg	
						Antimony (metallic)	0.010000000000	7440-36-0	CAS	0.100000000000	mg	
						Chromium	0.010000000000	7440-47-3	CAS	0.100000000000	mg	
						Manganese	0.020000000000	7439-96-5	CAS	0.200000000000	mg	
						Lead	0.050000000000	7439-92-1	CAS	0.500000000000	mg	
						Iron	0.100000000000	7439-89-6	CAS	1.000000000000	mg	
Phosphorous	0.100000000000	7723-14-0	CAS	1.000000000000	mg							



						Cobalt	0.1000000000 00	7440-48-4	CAS	1.00000 000000 0	mg	
						Nickel	0.1000000000 00	7440-02-0	CAS	1.00000 000000 0	mg	
						Zinc	0.3000000000 00	7440-66-6	CAS	3.00000 000000 0	mg	
						Tin	4.5000000000 00	7440-31-5	CAS	45.0000 000000 00	mg	
						Copper	94.698500000 000	7440-50-8	CAS	946.985 000000 000	mg	
Base Metals TEC-10 0-221A00 14	1.00 000 000 0											
		100-221	100.000000 000000	1000.0000 0000000	mg							
						Mercury	0.0005000000 00	7439-97-6	CAS	0.00500 000000 0	mg	
						Beryllium	0.0010000000 00	7440-41-7	CAS	0.01000 000000 0	mg	
						Arsenic	0.0050000000 00	7440-38-2	CAS	0.05000 000000 0	mg	
						Cadmium	0.0050000000 00	7440-43-9	CAS	0.05000 000000 0	mg	
						Antimony (metallic)	0.0100000000 00	7440-36-0	CAS	0.10000 000000 0	mg	
						Chromium	0.0100000000 00	7440-47-3	CAS	0.10000 000000 0	mg	
						Manganese	0.0200000000 00	7439-96-5	CAS	0.20000 000000 0	mg	



						Lead	0.0500000000 00	7439-92-1	CAS	0.50000 000000 0	mg	
						Iron	0.1000000000 00	7439-89-6	CAS	1.00000 000000 0	mg	
						Phosphorous	0.1000000000 00	7723-14-0	CAS	1.00000 000000 0	mg	
						Cobalt	0.1000000000 00	7440-48-4	CAS	1.00000 000000 0	mg	
						Nickel	0.1000000000 00	7440-02-0	CAS	1.00000 000000 0	mg	
						Zinc	0.3000000000 00	7440-66-6	CAS	3.00000 000000 0	mg	
						Tin	4.5000000000 00	7440-31-5	CAS	45.0000 000000 00	mg	
						Copper	94.698500000 000	7440-50-8	CAS	946.985 000000 000	mg	
112-25-3, PLATING,NICKE L,ELECTRODEPO SIT2288478-3 7	0.00 004 211 0											
		Nickel Plate	100.000000 000000	0.0421100 00000	mg							
						Cadmium	0.0075000000 00	7440-43-9	CAS	0.00000 315825 0	mg	
						Lead	0.0699000000 00	7439-92-1	CAS	0.00002 943489 0	mg	
						CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	0.2000000000 00	TE5081-2-032 0	CAS	0.00008 422000 0	mg	
						Nickel	99.722600000 000	7440-02-0	CAS	0.04199 318686 0	mg	



112-25-3, PLATING, NICKEL, ELECTRODEPOSITION 2288478-38	0.0004210											
		Nickel Plate	100.000000000000	0.04211000000	mg							
						Cadmium	0.007500000000	7440-43-9	CAS	0.00003158250	mg	
						Lead	0.069900000000	7439-92-1	CAS	0.000029434890	mg	
						CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	0.200000000000	TE5081-2-0320	CAS	0.000084220000	mg	
						Nickel	99.722600000000	7440-02-0	CAS	0.041993186860	mg	
TEC-112-65-1, PLATING, TIN (LEAD-FREE)2288474-19	0.00076300											
		Tin Plate	100.000000000000	0.76300000000	mg							
						Lead	0.070000000000	7439-92-1	CAS	0.000534100000	mg	
						CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	0.200000000000	TE5081-2-0320	CAS	0.001526000000	mg	
						Tin	99.730000000000	7440-31-5	CAS	0.760939900000	mg	
TEC-112-65-1, PLATING, TIN (LEAD-FREE)2288474-110	0.00076300											



		Tin Plate	100.000000 000000	0.7630000 00000	mg						
						Lead	0.0700000000 00	7439-92-1	CAS	0.00053 410000 0	mg
						CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	0.2000000000 00	TE5081-2-032 0	CAS	0.00152 600000 0	mg
						Tin	99.7300000000 000	7440-31-5	CAS	0.76093 990000 0	mg
112-162-5, PLATING, GOLD, ELECTRODEPOSI T2288504-5 11	0.00 006 860 0										
		Gold Plate	100.000000 000000	0.0686000 00000	mg						
						CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	0.3000000000 00	TE5081-2-032 0	CAS	0.00020 580000 0	mg
						Gold	99.7000000000 000	7440-57-5	CAS	0.06839 420000 0	mg
112-162-5, PLATING, GOLD, ELECTRODEPOSI T2288504-5 12	0.00 006 860 0										
		Gold Plate	100.000000 000000	0.0686000 00000	mg						
						CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	0.3000000000 00	TE5081-2-032 0	CAS	0.00020 580000 0	mg
						Gold	99.7000000000 000	7440-57-5	CAS	0.06839 420000 0	mg



Polyester Compound157 3755-1	4.39 900 000 0											
		1573755-1	100.000000 000000	4399.0000 00000000	mg							
						Arsenic	0.0020000000 00	7440-38-2	CAS	0.08798 000000 0	mg	
						Lead oxide (lead monoxide)	0.0020000000 00	1317-36-8	CAS	0.08798 000000 0	mg	
						Quartz (SiO2)	0.0050000000 00	14808-60-7	CAS	0.21995 000000 0	mg	
						Methylene chloride	0.0050000000 00	75-09-2	CAS	0.21995 000000 0	mg	
						Lead	0.0050000000 00	7439-92-1	CAS	0.21995 000000 0	mg	
						tetrahydrofuran	0.0500000000 00	109-99-9	CAS	2.19950 000000 0	mg	
						zinc oxide	0.0500000000 00	1314-13-2	CAS	2.19950 000000 0	mg	
						Copper oxide	0.0500000000 00	1317-38-0	CAS	2.19950 000000 0	mg	
						1,4-Benzenedicarboxylic acid	0.0500000000 00	100-21-0	CAS	2.19950 000000 0	mg	
						SILICA, AMORPHOUS	0.3000000000 00	112926-00-8	CAS	13.1970 000000 00	mg	
						trizinc bis(orthophosphate)	0.5000000000 00	7779-90-0	CAS	21.9950 000000 00	mg	
						Polytetrafluoroethylene	1.0000000000 00	9002-84-0	CAS	43.9900 000000 00	mg	



					Carbon-Black	3.0000000000 00	1333-86-4	CAS	131.970 000000 000	mg	
					Talc	3.0000000000 00	14807-96-6	CAS	131.970 000000 000	mg	
					Antimony trioxide	5.0000000000 00	1309-64-4	CAS	219.950 000000 000	mg	
					CONTAINS NO REPORTABLE TE5081-2 SUBSTANCES	8.0000000000 00	TE5081-2-032 0	CAS	351.920 000000 000	mg	
					AROMATIC BROMINATED FLAME RETARDANT WITH ANTIMONY - ISO 1043-4 CODE #FR(17)	13.0000000000 000			571.870 000000 000	mg	
					Fibrous-Glass-Wool	32.0000000000 000	65997-17-3	CAS	1407.68 000000 0000	mg	
					POLY(1,4-BUTYLENE TEREPHTHALATE)	33.9810000000 000	26062-94-2	CAS	1494.82 419000 0000	mg	