



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2014-07-18	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1934222-1	Amount	11616.11776	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1934707-1				4.0	2256.02944	mg	
Material	2	Tin Plate				4.0	0.779202	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	4.0	7.7842E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	4.0	0.77842	mg	
Material	2	Gold Plate				4.0	0.406714	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	4.0	0.40549	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	4.0	0.00122014	mg	
Material	2	LCP-(GF20+T20)				4.0	1429.1088	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	2.0	4.0	28.58218	mg	
Substance	3	Carbon black	Supplier	1333-86-4	5.0	4.0	71.45544	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	20.0	4.0	285.82176	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	4.0	285.82176	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	53.0	4.0	757.42766	mg	
Material	2	Nickel Plate				4.0	34.534724	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.06906945	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	0.03453472	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	34.43112	mg	
Material	2	Phos Bronze				4.0	791.2	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	4.0	749.13585	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.15824	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	0.07912	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	4.0	35.604	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	4.0	0.11868	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.07912	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.7912	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	0.007912	mg	

Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	2.3736	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	4.0	0.7912	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.7912	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	4.0	0.07912	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.3956	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.7912	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	0.003956	mg	
Sub-Item	1	1469694-1				1.0	2592.0	mg	
Material	2	LCP-(GF10+MD20)				1.0	2592.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.996	1.0	51.73632	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	25.92	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	22.0	1.0	570.24	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	10.0	1.0	259.2	mg	
Substance	3	Phenol	Supplier	108-95-2	0.0040	1.0	0.10368	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	65.0	1.0	1684.8	mg	