



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	485203835	Response Date	2014-09-08	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1-66105-9	Amount	428.682	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	380579-2				1.0	28.23	mg																										
Material	2	Brass				1.0	27.87	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	2.787E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	7.80987	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.013935	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.002787	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.013935	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.02787	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.787E-4	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	19.92705	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.002787	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.3935E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.05574	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0013935	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.013935	mg																										
Material	2	Nickel Plate				1.0	0.36	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	7.2E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.6E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.35892	mg																										
Sub-Item	1	788086-1				1.0	48.26	mg																										
Material	2	Stainless Steel				1.0	48.26	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.004826	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.35	1.0	0.16891	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.826E-4	mg																										
Substance	3	Silicon	Supplier	7440-21-3	1.0	1.0	0.4826	mg																										
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	0.9652	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.05	1.0	0.02413	mg																										
Substance	3	Chromium	Supplier	7440-47-3	19.0	1.0	9.1694	mg																										
Substance	3	Iron	Supplier	7439-89-6	66.4885	1.0	32.08735	mg																										
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.07239	mg																										
Substance	3	Molybdenum	Supplier	7439-98-7	0.8	1.0	0.38608	mg																										
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.014478	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.004826	mg																										

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.004826	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.413E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	1.0	4.826	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04826	mg	
Sub-Item	1	2-66095-5				1.0	352.192	mg	
Material	2	Brass				1.0	340.86	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0034086	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	95.51749	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.17043	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.034086	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.17043	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.34086	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0034086	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	243.7149	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.034086	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0017043	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.68172	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.017043	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.17043	mg	
Material	2	Nickel Plate				1.0	3.277	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.006554	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.003277	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	3.26717	mg	
Material	2	Tin Plate				1.0	8.055	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00804694	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	8.04695	mg	