



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer		
Company Unique ID	485203835	Response Date	2014-06-17	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-102154-0	Amount	10135.0841783	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	102142-5				1.0	7610.0	mg	
Material	2	PBT-GF30FR(17)				1.0	7610.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	2283.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	2511.3	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	76.1	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	76.1	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	380.5	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	2283.0	mg	
Sub-Item	1	102129-3				50.0	50.50168357	mg	
Material	2	Nickel Plate				50.0	0.0279919	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	5.59838E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	2.79919E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	0.02790792	mg	
Material	2	Gold Plate				50.0	0.0022355	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	50.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.00222879	mg	
Material	2	Brass				50.0	50.46	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	50.0	0.05046	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	50.0	32.2944	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	50.0	0.02523	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	50.0	0.005046	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	5.046E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	0.05046	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	50.0	0.05046	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	50.0	17.76621	mg	

Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	0.005046	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	50.0	0.005046	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	50.0	0.02523	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	50.0	0.15138	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	2.523E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	50.0	0.005046	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	50.0	0.02523	mg	
Material	2	Tin-Lead Plate				50.0	0.00806907	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	50.0	5.6483E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	50.0	0.00744775	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	50.0	5.648346E-5	mg	
Material	2	Gold Plate				50.0	0.0033871	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.00337694	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	1.01613E-5	mg	