



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-07-05	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-66358-6	<b>Amount</b>	621.102	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	788086-1				1.0	48.26	mg	
Material	2	Stainless Steel				1.0	48.26	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.004826	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.35	1.0	0.16891	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.826E-4	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.0	1.0	0.4826	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	0.9652	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.05	1.0	0.02413	mg	
Substance	3	Chromium	Supplier	7440-47-3	19.0	1.0	9.1694	mg	
Substance	3	Iron	Supplier	7439-89-6	66.4885	1.0	32.08735	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.07239	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.8	1.0	0.38608	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.014478	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.004826	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.004826	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.413E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	1.0	4.826	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04826	mg	
Sub-Item	1	380579-2				1.0	28.23	mg	
Material	2	Nickel Plate				1.0	0.36	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	7.2E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.6E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.35892	mg	
Material	2	Brass				1.0	27.87	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	2.787E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	7.80987	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.013935	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.002787	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.013935	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.02787	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.787E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	19.92705	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.002787	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.3935E-4	mg	

Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.05574	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0013935	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.013935	mg	
Sub-Item	1	1-66356-6				1.0	544.612	mg	
Material	2	Nickel Plate				1.0	4.3	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0086	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0043	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	4.2871	mg	
Material	2	Brass				1.0	529.51	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0052951	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	148.38194	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.26475	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.052951	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.26475	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.52951	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0052951	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	378.59965	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.052951	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00264755	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.05902	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0264755	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.26475	mg	
Material	2	Tin Plate				1.0	10.802	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.0107912	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	10.79121	mg	