



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2014-06-04	Contact Email	dave.benfer@te.com																													
Contact Phone Number		7179863725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1-338088-3	Amount	2.64244502	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	338090-1				1.0	0.33454838	g																										
Material	2	LCP-GF30				1.0	0.301875	g																										
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	68.6	1.0	0.20708625	g																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.0905625	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.4	1.0	0.0012075	g																										
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.00301875	g																										
Material	2	Phos Bronze				1.0	0.03267338	g																										
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	0.0309363	g																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	6.534675E-6	g																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	3.267338E-6	g																										
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	0.0014703	g																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	4.901006E-6	g																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	3.267338E-6	g																										
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	3.267338E-5	g																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	3.267338E-7	g																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	9.802013E-5	g																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	3.267338E-5	g																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.267338E-5	g																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	3.267338E-6	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.633669E-5	g																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	3.267338E-5	g																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.633669E-7	g																										
Sub-Item	1	338089-1				1.0	1.427	g																										
Material	2	PA9T-GF33				1.0	1.427	g																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.1	1.0	0.044237	g	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 2-methyl-1,8-octanediamine and 1,9-nonanediamine	Supplier	169284-22-4	42.2	1.0	0.602194	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.2	1.0	0.002854	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	0.007135	g	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	20.9	1.0	0.298243	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.3	1.0	0.004281	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	32.8	1.0	0.468056	g	
Sub-Item	1	338093-3				1.0	0.338305	g	
Material	2	Gold Plate				1.0	0.00128	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.00127616	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	3.84E-6	g	
Material	2	Tin Plate				1.0	0.023357	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	2.333364E-5	g	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.02333367	g	
Material	2	Nickel Plate				1.0	0.019168	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	3.8336E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.9168E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.0191105	g	
Material	2	Phos Bronze				1.0	0.2945	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.945E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	2.945E-5	g	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	5.89E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	4.4175E-5	g	
Substance	3	Copper	Supplier	7440-50-8	90.0335	1.0	0.26514866	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.00103075	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	5.89E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.945E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	2.945E-5	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	2.945E-4	g	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	0.026505	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	2.945E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.4725E-6	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	2.945E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.4725E-4	g	
Sub-Item	1	338138-1				1.0	0.54259165	g	
Material	2	Brass				1.0	0.52709003	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	5.2709E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	0.1477038	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	2.6355E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	5.2709E-5	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	2.6355E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	5.2709E-4	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.2709E-6	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	0.37686937	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	5.2709E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.63545E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.00105418	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.63545E-5	g	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.6355E-4	g	
Material	2	Tin Plate				1.0	0.01031052	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	1.030021E-5	g	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.01030022	g	
Material	2	Nickel Plate				1.0	0.0051911	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	1.03822E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	5.1911E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.00517553	g	