



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A		
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	PROD COMPLIANCE ENGINEER		
<b>Company Unique ID</b>	-	<b>Response Date</b>	2013-05-09	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	(86)21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-770968-0	<b>Amount</b>	2588.368	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>REACH-0209</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	770955-1				1.0	1919.8	mg	
Material	2	PA6+PA66				1.0	1919.8	mg	
Substance	3	Nitrogen compounds - ISO 1043-4 code #FR(30)	Supplier	1043-4-FR30	9.0	1.0	172.782	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	38.396	mg	
Substance	3	Polyamide Polymer Blend - ISO 1043-1 Term PA66+PA6	Supplier	1043-1-PA66+PA6	89.0	1.0	1708.622	mg	
Sub-Item	1	770603-4				2.0	135.761	mg	
Material	2	Tin Plate				2.0	2.83	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	2.0	2.81585	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	2.0	0.01132	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00283	mg	
Material	2	Brass				2.0	132.24	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	94.5516	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.0013224	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	2.0	37.02389	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.06612	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.0013224	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.06612	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.13224	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.013224	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.013224	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.092568	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.013224	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	6.612E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.26448	mg	
Material	2	Nickel Plate				2.0	0.691	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	0.001382	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	6.91E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.68893	mg	
Sub-Item	1	770604-4				2.0	198.523	mg	
Material	2	Tin Plate				2.0	8.065	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	2.0	8.02468	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	2.0	0.03226	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.008065	mg	
Material	2	Brass				2.0	188.49	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	134.77035	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.0018849	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	2.0	52.77249	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.094245	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.0018849	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.094245	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.18849	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.018849	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.018849	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.13194	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.018849	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	9.4245E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.37698	mg	
Material	2	Nickel Plate				2.0	1.968	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	0.003936	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.001968	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	1.9621	mg	