



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A																	
Supplier Information																										
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer																			
Company Unique ID	1473	Response Date	2014-03-24	Contact Email	cc.wu@te.com																					
Contact Phone Number	021-33980068																									
Legal Statement																										
Supplier Acceptance	true																									
Legal Statement																										
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																										
Product																										
Manufacturer Item number	1-794068-0	Amount	4.65605897	Version	-	Identity																				
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority																				
Date		UOM	Each																							
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																									
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																									
Manufacturing Information																										
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info																				
Classification Temp		Max Wave Solder Time	10.0	Ramp Down Rate		Psl Rating Reflow																				
Max Time Within 5		Psl Rating Wave		Package Designator		Size	0.0																			
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC																			
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC																			
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC																			
Product Disclosure																										
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																	
Sub-Item	1	770162-4				16.0	0.113664	g																		
Material	2	Nickel Plate				16.0	6.05E-4	g																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	16.0	1.21E-6	g																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	16.0	6.05E-7	g																		
Substance	3	Nickel	Nickel	7440-02-0	99.7	16.0	6.0319E-4	g																		
Material	2	Tin Plate				16.0	0.002059	g																		
Substance	3	Tin	Supplier	7440-31-5	99.5	16.0	0.0020487	g																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	16.0	8.236E-6	g																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	16.0	2.059E-6	g																		
Material	2	Brass				16.0	0.111	g																		
Substance	3	Chromium	Supplier	7440-47-3	0.0010	16.0	1.11E-6	g																		
Substance	3	Zinc	Supplier	7440-66-6	28.0225	16.0	0.03110497	g																		
Substance	3	Manganese	Supplier	7439-96-5	0.05	16.0	5.55E-5	g																		
Substance	3	Antimony	Supplier	7440-36-0	0.01	16.0	1.11E-5	g																		
Substance	3	Iron	Supplier	7439-89-6	0.05	16.0	5.55E-5	g																		
Substance	3	Cobalt	Supplier	7440-48-4	0.1	16.0	1.11E-4	g																		
Substance	3	Copper	Supplier	7440-50-8	71.5	16.0	0.079365	g																		
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	16.0	1.11E-6	g																		
Substance	3	Arsenic	Supplier	7440-38-2	0.01	16.0	1.11E-5	g																		
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	16.0	5.55E-7	g																		
Substance	3	Nickel	Nickel	7440-02-0	0.2	16.0	2.22E-4	g																		

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	16.0	5.55E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	16.0	5.55E-5	g	
Sub-Item	1	794083-1				1.0	2.83743497	g	
Material	2	PA				1.0	2.83743497	g	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	0.00925571	g	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	0.01315719	g	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	8.512305E-6	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	0.9451	1.0	0.0268166	g	
Substance	3	Benzenepropionamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	0.01136109	g	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	9.363535E-5	g	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	7.0936E-4	g	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	0.00570892	g	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.1901	1.0	0.00539396	g	
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	0.25740359	g	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	2.5075264	g	