



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Manager Environmental Engineering		
Company Unique ID	485203835	Response Date	2014-05-05	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	104068-4	Amount	2371.0	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	103917-2				40.0	22.81	mg	
Material	2	Tin-Lead Plate				40.0	0.49	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	40.0	0.45227	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	40.0	0.00343	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	40.0	0.0343	mg	
Material	2	Phos Bronze				40.0	21.77	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	40.0	20.6126	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	40.0	0.004354	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	40.0	0.002177	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	40.0	0.97965	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	40.0	0.0032655	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	0.002177	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	40.0	0.02177	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	2.177E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	40.0	0.06531	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	40.0	0.02177	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	0.02177	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	40.0	0.002177	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.010885	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	40.0	0.02177	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	1.0885E-4	mg	
Material	2	Nickel Plate				40.0	0.21	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	4.2E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	2.1E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.20937	mg	
Material	2	Gold Plate				40.0	0.17	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	5.1E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.16949	mg	
Material	2	Gold Plate				40.0	0.17	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.16949	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	40.0	5.1E-4	mg	
Sub-Item	1	1-104034-7				1.0	1458.6	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	1458.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	43.758	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	977.262	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	437.58	mg	