



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Manager Environmental Engineering		
Company Unique ID	485203835	Response Date	2014-05-05	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	104078-2	Amount	2070.563454	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	146101-2				40.0	27.2862154	mg	
Material	2	Tin-Lead Plate				40.0	0.233522	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	40.0	0.21554	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	40.0	0.00163465	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	40.0	0.01634654	mg	
Material	2	Gold Plate				40.0	0.0628034	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.06261499	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	40.0	1.8841E-4	mg	
Material	2	Nickel Plate				40.0	0.68989	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	0.00137978	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	6.8989E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.68782	mg	
Material	2	Phos Bronze				40.0	26.3	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	40.0	24.90176	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	40.0	0.00526	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	40.0	0.00263	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	40.0	1.1835	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	40.0	0.003945	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	0.00263	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	40.0	0.0263	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	2.63E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	40.0	0.0789	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	40.0	0.0263	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	0.0263	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	40.0	0.00263	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.01315	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	40.0	0.0263	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	1.315E-4	mg	
Sub-Item	1	1-104002-2				1.0	979.114838	mg	

Material	2	LIQUID CRYSTAL PLOYMER				1.0	979.114838	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 0909	3.0	1.0	29.37345	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	656.00694	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	293.73445	mg	