



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	485203835	Response Date	2014-07-03	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1060904-1	Amount	1126.168771	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s) - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	3-1403081-3				1.0	61.696	mg	
Material	2	Nickel Plate				1.0	1.26	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00126	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00252	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.25622	mg	
Material	2	Brass				1.0	60.1	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	6.01E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00601	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0601	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00601	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.01202	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	6.01E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	1.0	0.21035	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	1.0	19.68125	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	1.0	37.863	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.005E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	2.2237	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.00601	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.03005	mg	
Material	2	Copper Plate				1.0	0.336	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.36E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	0.33566	mg	
Sub-Item	1	1406695-2				1.0	27.913068	mg	
Material	2	Nickel Plate				1.0	0.375623	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	7.5125E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.7562E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.3745	mg	
Material	2	Brass				1.0	26.6	mg	

Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.66E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00266	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0266	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00266	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.00532	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	2.66E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	1.0	0.0931	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	1.0	8.71083	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	1.0	16.758	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.33E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	0.9842	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.00266	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.0133	mg	
Material	2	Gold Plate				1.0	0.173785	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	5.2136E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.17326	mg	
Material	2	Copper Plate				1.0	0.198859	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.9886E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	0.19866	mg	
Material	2	Gold Plate				1.0	0.564801	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.56311	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.0016944	mg	
Sub-Item	1	1406635-2				1.0	462.877593	mg	
Material	2	Nickel Plate				1.0	7.555952	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00755595	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0151119	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	7.53328	mg	
Material	2	Brass				1.0	452.895595	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00452896	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.04528956	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.4529	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.04528956	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.09057912	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00452896	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	1.0	1.58513	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	1.0	148.31198	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	1.0	285.32422	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00226448	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	16.75714	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.04528956	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.22645	mg	
Material	2	Copper Plate				1.0	2.426046	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00242605	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	2.42362	mg	
Sub-Item	1	1406926-1				1.0	46.509793	mg	
Material	2	Teflon				1.0	46.509793	mg	
Substance	3	1-Propene, 1,1,2,3,3,3-hexafluoro-, polymer with 1,1,2,2-tetrafluoroethene	Supplier	25067-11-2	100.0	1.0	46.50979	mg	

Sub-Item	1	1406315-1				1.0	7.853756	mg	
Material	2	Teflon				1.0	7.853756	mg	
Substance	3	1-Propene, 1,1,2,3,3,3-hexafluoro-, polymer with 1,1,2,2-tetrafluoroethene	Supplier	25067-11-2	100.0	1.0	7.85376	mg	
Sub-Item	1	6-1403102-9				1.0	431.4223	mg	
Material	2	Nickel Plate				1.0	6.0265	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0060265	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.012053	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	6.00842	mg	
Material	2	Brass				1.0	423.4609	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00423461	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	118.66433	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.21173	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.04234609	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.21173	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.42346	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00423461	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	302.77454	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.04234609	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0021173	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.84692	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.02117305	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.21173	mg	
Material	2	Copper Plate				1.0	1.9349	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0019349	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	1.93297	mg	
Sub-Item	1	1406008-5				1.0	87.896261	mg	
Material	2	Nickel Plate				1.0	2.020681	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00404136	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00202068	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.01462	mg	
Material	2	Beryllium Copper				1.0	81.3	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00813	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	1.0	0.4878	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	8.13E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	1.0	1.626	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.01626	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	1.0	0.4878	mg	
Substance	3	Copper	Supplier	7440-50-8	96.0485	1.0	78.08743	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00813	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.6	1.0	0.4878	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.00813	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.065E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0813	mg	
Material	2	Gold Plate				1.0	0.934882	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.00280465	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.93208	mg	
Material	2	Copper Plate				1.0	1.069772	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00106977	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	1.0687	mg	
Material	2	Gold Plate				1.0	2.570926	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	2.56321	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.00771278	mg	
-----------	---	--	----------	---------------	-----	-----	------------	----	--