



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A		
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	-	Response Date	2013-05-03	Contact Email	cc.wu@te.com				
Contact Phone Number	(86)21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	102153-4	Amount	4735.195944	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products								
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	102129-2				20.0	51.8597972	mg	
Material	2	Gold Plate				20.0	0.043016	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	0.04288695	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	20.0	1.2905E-4	mg	
Material	2	Nickel Plate				20.0	1.03	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	20.0	0.00206	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	0.00103	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	20.0	1.02691	mg	
Material	2	Brass				20.0	50.46	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	20.0	0.05046	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	20.0	32.2944	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	20.0	0.02523	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	20.0	5.046E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	20.0	0.005046	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	20.0	0.05046	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	20.0	0.05046	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	20.0	17.76621	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	20.0	0.005046	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	20.0	0.005046	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	20.0	0.02523	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	20.0	0.15138	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	20.0	0.005046	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	20.0	2.523E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	20.0	0.02523	mg	
Material	2	Tin-Lead Plate				20.0	0.27	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	20.0	0.0189	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	20.0	0.24921	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	20.0	0.00189	mg	
Material	2	Gold Plate				20.0	0.0567812	mg	

Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	0.05661086	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	20.0	1.7034E-4	mg	
Sub-Item	1	102142-1				1.0	3698.0	mg	
Material	2	PBT-GF30FR(17)				1.0	3698.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4'-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	1109.4	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	1220.34	mg	
Substance	3	Antimony oxide (Sb ₂ O ₃)	Supplier	1309-64-4	5.0	1.0	184.9	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	36.98	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	36.98	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1109.4	mg	