



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	485203835	Response Date	2013-11-11	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1658686-2	Amount	88.644348	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Gold Plate				1.0	0.119584	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	0.11923	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	3.5875E-4	mg	
Material	1	Tin Plate				1.0	0.801179	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	8.0038E-4	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9001	1.0	0.80038	mg	
Material	1	Nickel Plate				1.0	1.423585	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.00284717	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00142358	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.7	1.0	1.41931	mg	
Material	1	Phos Bronze				1.0	86.3	mg	
Substance	2	Copper	Supplier	7440-50-8	94.6835	1.0	81.71186	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.01726	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.01	1.0	0.00863	mg	
Substance	2	Tin	Supplier	7440-31-5	4.5	1.0	3.8835	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.015	1.0	0.012945	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	0.0863	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.00863	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	8.63E-4	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.3	1.0	0.2589	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.0863	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0863	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.00863	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.04315	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.1	1.0	0.0863	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.315E-4	mg	