



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	485203835	Response Date	2013-12-04	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	104074-1	Amount	895.368742	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	103917-6				10.0	13.0	mg	
Material	2	Gold Plate				10.0	0.01032	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.01028904	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	3.096E-5	mg	
Material	2	Phos Bronze				10.0	12.830397	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	10.0	12.14827	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.00256608	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.00128304	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	10.0	0.57737	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	10.0	0.00192456	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.0128304	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.00128304	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	1.283E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.03849119	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	10.0	0.0128304	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.0128304	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.00128304	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.0064152	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.0128304	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	6.415199E-5	mg	
Material	2	Tin-Lead Plate				10.0	0.149	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	10.0	0.001043	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	10.0	0.13753	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	10.0	0.01043	mg	
Material	2	Nickel Plate				10.0	0.004413	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	10.0	1.0E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	1.0E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.00439976	mg	
Material	2	Gold Plate				10.0	0.00587	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.00585239	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	1.761E-5	mg	
Sub-Item	1	103913-2				2.0	33.0005	mg	
Material	2	Phos Bronze				2.0	29.744	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	2.0	28.16266	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0059488	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.0029744	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	2.0	1.33848	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	2.0	0.0044616	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.029744	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0029744	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	2.9744E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	2.0	0.089232	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	2.0	0.029744	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.029744	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0029744	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.014872	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.029744	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.4872E-4	mg	
Material	2	Tin-Lead Plate				2.0	2.26	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	2.0	0.01582	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	2.0	2.08598	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	2.0	0.1582	mg	
Material	2	Nickel Plate				2.0	0.9965	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	0.001993	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	9.965E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.99351	mg	
Sub-Item	1	104075-1				1.0	699.367742	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	699.367742	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	20.98103	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	468.57639	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	209.81032	mg	