



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Engineer Product Compliance china		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-05-13	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	86-2124071672								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	170362-3	<b>Amount</b>	183.0	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Brass				1.0	180.387	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00180387	mg	
Substance	2	Zinc	Supplier	7440-66-6	28.0225	1.0	50.54895	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.05	1.0	0.0901935	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.0180387	mg	
Substance	2	Iron	Supplier	7439-89-6	0.05	1.0	0.0901935	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.18039	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00180387	mg	
Substance	2	Copper	Supplier	7440-50-8	71.5	1.0	128.97671	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0180387	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.0193E-4	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.2	1.0	0.36077	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00901935	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0901935	mg	
Material	1	Nickel Plate				1.0	2.323	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.004646	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.002323	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.7	1.0	2.31603	mg	
Material	1	Gold Plate				1.0	0.29	mg	
Substance	2	Gold	Supplier	7440-57-5	99.0	1.0	0.2871	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	0.0029	mg	