



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Kiwi Lee	Contact Title	Senior Engineer Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2014-11-19	Contact Email	kiwi.lee@te.com				
Contact Phone Number	886-2-87682788								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1734035-1	Amount	688.0	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Housing_PA9T				1.0	137.0	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	4.11	mg	
Substance	2	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	22.0	1.0	30.14	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	47.95	mg	
Substance	2	1,4-Benzenedicarb oxylic acid, polymer with 2-methyl-1,8-octanediamine and 1,9-nonanediamine	Supplier	169284-22-4	40.0	1.0	54.8	mg	
Material	1	Shell_Ni Plating				1.0	0.3	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.8	1.0	0.2994	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	6.0E-4	mg	
Material	1	Contact_Sn Plating				1.0	1.5	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	1.5	mg	
Material	1	Shell_Cu Plating				1.0	0.3	mg	
Substance	2	Copper	Supplier	7440-50-8	100.0	1.0	0.3	mg	
Material	1	Shell_C5191				1.0	498.4	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.3	1.0	1.4952	mg	
Substance	2	Tin	Supplier	7440-31-5	7.0	1.0	34.888	mg	
Substance	2	Copper	Supplier	7440-50-8	92.7	1.0	462.0168	mg	
Material	1	Contact_Ni Plating				1.0	1.5	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0030	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.8	1.0	1.497	mg	
Material	1	Contact_Pd-Ni Plating				1.0	1.5	mg	
Substance	2	Palladium	Supplier	7440-05-3	80.0	1.0	1.2	mg	
Substance	2	Nickel	Nickel	7440-02-0	20.0	1.0	0.3	mg	

Material	1	Contact_Au Plating				1.0	1.5	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.15	1.0	0.00225	mg	
Substance	2	Gold	Supplier	7440-57-5	99.85	1.0	1.49775	mg	
Material	1	Contact_C519 1				1.0	46.0	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.3	1.0	0.138	mg	
Substance	2	Tin	Supplier	7440-31-5	7.0	1.0	3.22	mg	
Substance	2	Copper	Supplier	7440-50-8	92.7	1.0	42.642	mg	