



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	M. Global Product Compliance		
Company Unique ID	485203835	Response Date	2014-07-21	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	104652-3	Amount	992.7054818	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	104653-2				30.0	4.5	mg	
Material	2	Copper Alloy				30.0	4.13921	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	30.0	0.0020696	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	30.0	0.0413921	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	30.0	0.04967052	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	30.0	0.00413921	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7635	30.0	3.83968	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	30.0	0.00248353	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	30.0	4.13921E-5	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	30.0	0.01241763	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	30.0	0.00413921	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	30.0	0.00827842	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	30.0	4.1392E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	30.0	4.1392E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	30.0	0.17385	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	30.0	2.0696E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	30.0	2.069605E-5	mg	
Material	2	Gold Plate				30.0	0.05179	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	30.0	0.05163463	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	30.0	1.5537E-4	mg	
Material	2	Nickel Plate				30.0	0.236	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	30.0	4.72E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	30.0	2.36E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	30.0	0.23529	mg	
Material	2	Tin-Lead Plate				30.0	0.073	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	30.0	0.067379	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	30.0	5.11E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	30.0	0.00511	mg	

Sub-Item	1	104794-3				1.0	799.28	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	799.28	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	23.9784	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	535.5176	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	239.784	mg	
Sub-Item	1	104783-2				2.0	29.2127409	mg	
Material	2	Nickel Plate				2.0	0.2340809	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	4.6816E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	2.3408E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.23338	mg	
Material	2	Tin-Lead Plate				2.0	0.34166	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	2.0	0.31535	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	2.0	0.00239162	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	2.0	0.0239162	mg	
Material	2	Beryllium Copper				2.0	28.637	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	2.0	0.57274	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0028637	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0057274	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.2	2.0	0.057274	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.2	2.0	0.057274	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	2.0	0.11455	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0028637	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	0.057274	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	2.8637E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	96.649	2.0	27.67737	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.028637	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.057274	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00143185	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.4318E-4	mg	