



|   |   |   |                           |                      |                                |                      |                                |                      |                  |
|---|---|---|---------------------------|----------------------|--------------------------------|----------------------|--------------------------------|----------------------|------------------|
| <b>Form Type</b>  | Distribute  | <b>Version</b>  | 2.0                       | <b>Ref</b>           | IPC 1752A                      | <b>Sectionals</b>    | Material Info                  | <b>Subsectionals</b> | D, A             |
| <b>Supplier Information</b>   |   |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Company Name</b>   | TE Connectivity   | <b>Request Document ID</b>  |                           | <b>Contact Name</b>  | John R. Penica                 | <b>Contact Title</b> | Mgr. Global Product Compliance |                      |                  |
| <b>Company Unique ID</b>  | TE Connectivity   | <b>Response Date</b>  | 2015-02-03                | <b>Contact Email</b> | jrpenica@te.com                |                      |                                |                      |                  |
| <b>Contact Phone Number</b>   | 717-592-3266  |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Legal Statement</b>  |   |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Supplier Acceptance</b>  | true  |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Legal Statement</b>  |   |   |                           |                      |                                |                      |                                |                      |                  |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. |   |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Product</b>  |   |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Manufacturer Item number</b>   | 163681-2  | <b>Amount</b>   | 0.522756                  | <b>Version</b>       | -                              | <b>Identity</b>      |                                |                      |                  |
| <b>Manufacturer Item Name</b>   | 04P.CIS FEMALE CONN   | <b>Weight Uom</b>   | g                         | <b>Mfr Site</b>      |                                | <b>Authority</b>     |                                |                      |                  |
| <b>Date</b>   |   | <b>UOM</b>  | Each                      |                      |                                |                      |                                |                      |                  |
| <b>EUroHS-0508</b>  | Product(s) meets EU RoHS requirement without any exemptions   |   |                           |                      |                                |                      |                                |                      |                  |
| <b>ChinaRoHS-0508</b>   | Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products |   |                           |                      |                                |                      |                                |                      |                  |
| <b>EUREACH-1213</b>   | REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH                           |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Product Disclosure</b>   |   |   |                           |                      |                                |                      |                                |                      |                  |
| <b>Sub-Item/Material/Substance</b>  | <b>Level</b>  | <b>Name</b>   | <b>Substance Category</b> | <b>Substance CAS</b> | <b>Substance Concentration</b> | <b>Quantity</b>      | <b>Mass per Unit</b>           | <b>UOM</b>           | <b>Exemption</b> |
| Sub-Item  | 1   | CIS FEMALE POST   |                           |                      |                                | 4.0                  | 0.124089                       | g                    |                  |
| Material  | 2   | Brass   |                           |                      |                                | 4.0                  | 0.124                          | g                    |                  |
| Substance   | 3   | Chromium  | Supplier                  | 7440-47-3            | 0.0010                         | 4.0                  | 1.24E-6                        | g                    |                  |
| Substance   | 3   | Zinc  | Supplier                  | 7440-66-6            | 28.0225                        | 4.0                  | 0.0347479                      | g                    |                  |
| Substance   | 3   | Manganese   | Supplier                  | 7439-96-5            | 0.05                           | 4.0                  | 6.2E-5                         | g                    |                  |
| Substance   | 3   | Antimony  | Supplier                  | 7440-36-0            | 0.01                           | 4.0                  | 1.24E-5                        | g                    |                  |
| Substance   | 3   | Iron  | Supplier                  | 7439-89-6            | 0.05                           | 4.0                  | 6.2E-5                         | g                    |                  |
| Substance   | 3   | Cobalt  | Supplier                  | 7440-48-4            | 0.1                            | 4.0                  | 1.24E-4                        | g                    |                  |
| Substance   | 3   | Beryllium   | Supplier                  | 7440-41-7            | 0.0010                         | 4.0                  | 1.24E-6                        | g                    |                  |
| Substance   | 3   | Copper  | Supplier                  | 7440-50-8            | 71.5                           | 4.0                  | 0.08866                        | g                    |                  |
| Substance   | 3   | Arsenic   | Supplier                  | 7440-38-2            | 0.01                           | 4.0                  | 1.24E-5                        | g                    |                  |
| Substance   | 3   | Mercury   | Mercury/Mercury Compounds | 7439-97-6            | 5.0E-4                         | 4.0                  | 6.2E-7                         | g                    |                  |
| Substance   | 3   | Nickel  | Nickel                    | 7440-02-0            | 0.2                            | 4.0                  | 2.48E-4                        | g                    |                  |
| Substance   | 3   | Cadmium   | Cadmium/Cadmium Compounds | 7440-43-9            | 0.0050                         | 4.0                  | 6.2E-6                         | g                    |                  |
| Substance   | 3   | Lead  | Lead/Lead Compounds       | 7439-92-1            | 0.05                           | 4.0                  | 6.2E-5                         | g                    |                  |
| Material  | 2   | Tin Plate   |                           |                      |                                | 4.0                  | 4.0E-5                         | g                    |                  |
| Substance   | 3   | Lead  | Lead/Lead Compounds       | 7439-92-1            | 0.0999                         | 4.0                  | 3.996E-8                       | g                    |                  |
| Substance   | 3   | Tin   | Supplier                  | 7440-31-5            | 99.9001                        | 4.0                  | 3.996004E-5                    | g                    |                  |
| Material  | 2   | Nickel Plate  |                           |                      |                                | 4.0                  | 4.9E-5                         | g                    |                  |
| Substance   | 3   | Contains No Reportable TE5081-2 Substances  | Supplier                  | TE5081-2-1212        | 0.2                            | 4.0                  | 9.8E-8                         | g                    |                  |
| Substance   | 3   | Lead  | Lead/Lead Compounds       | 7439-92-1            | 0.1                            | 4.0                  | 4.9E-8                         | g                    |                  |
| Substance   | 3   | Nickel  | Nickel                    | 7440-02-0            | 99.7                           | 4.0                  | 4.8853E-5                      | g                    |                  |
| Sub-Item  | 1   | 60P.CIS FEMALE HSG.   |                           |                      |                                | 0.066                | 0.4                            | g                    |                  |
| Material  | 2   | POLYESTER   |                           |                      |                                | 0.066                | 0.4                            | g                    |                  |
| Substance   | 3   | Chromium oxide (Cr2O3)  | Supplier                  | 1308-38-9            | 0.03                           | 0.066                | 1.2E-4                         | g                    |                  |
| Substance   | 3   | Any substance originating from animal tissues of bovine, ovine, caprine, deer, elk, mink and cats species | Supplier                  | TE-Animal byproduct  | 0.5                            | 0.066                | 0.0020                         | g                    |                  |

|           |   |   |          |               |       |       |         |   |  |
|-----------|---|---|----------|---------------|-------|-------|---------|---|--|
| Substance | 3 | Ethene, homopolymer   | Supplier | 9002-88-4     | 0.5   | 0.066 | 0.0020  | g |  |
| Substance | 3 | 1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol                   | Supplier | 26062-94-2    | 45.17 | 0.066 | 0.18068 | g |  |
| Substance | 3 | Phosphoric acid, calcium salt (2:3)   | Supplier | 7758-87-4     | 1.0   | 0.066 | 0.0040  | g |  |
| Substance | 3 | Zinc sulfide (ZnS)  | Supplier | 1314-98-3     | 1.0   | 0.066 | 0.0040  | g |  |
| Substance | 3 | Contains No Reportable TE5081-2 Substances                                  | Supplier | TE5081-2-1212 | 0.5   | 0.066 | 0.0020  | g |  |
| Substance | 3 | Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17) | Supplier | 1043-4-FR17   | 20.0  | 0.066 | 0.08    | g |  |
| Substance | 3 | Glass, oxide, chemicals   | Supplier | 65997-17-3    | 30.0  | 0.066 | 0.12    | g |  |
| Substance | 3 | C.I. Pigment Brown 24   | Supplier | 68186-90-3    | 0.2   | 0.066 | 8.0E-4  | g |  |
| Substance | 3 | C.I. Pigment Black 26   | Supplier | 68186-94-7    | 0.1   | 0.066 | 4.0E-4  | g |  |
| Substance | 3 | Ethene, 1,1,2,2-tetrafluoro-, homopolymer                                   | Supplier | 9002-84-0     | 1.0   | 0.066 | 0.0040  | g |  |