



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Kiwi Lee	Contact Title	Senior Engineer Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2014-11-04	Contact Email	kiwi.lee@te.com				
Contact Phone Number	886-2-87682788								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1981568-1	Amount	232.0	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1981742-1				1.0	190.0	mg	
Material	2	Stainless Steel				1.0	185.212	mg	
Substance	3	Chromium	Supplier	7440-47-3	18.0	1.0	33.33816	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.5	1.0	0.92606	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.045	1.0	0.0833454	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0185212	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.01	1.0	0.0185212	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.5	1.0	2.77818	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.27782	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	3.70424	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.03	1.0	0.0555636	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.0555636	mg	
Substance	3	Iron	Supplier	7439-89-6	68.6145	1.0	127.08229	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.18521	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0185212	mg	
Substance	3	Nickel	Nickel	7440-02-0	9.0	1.0	16.66908	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.2606E-4	mg	
Material	2	Nickel Plate				1.0	2.928	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.005856	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.002928	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.91922	mg	
Material	2	Tin Plate				1.0	1.86	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.00744	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	1.8507	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00186	mg	
Sub-Item	1	1981740-1				1.0	42.0	mg	
Material	2	LCP-(GF+MD)40				1.0	29.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	0.58	mg	

Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	26.5	1.0	7.685	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	12.7	1.0	3.683	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.29	mg	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	57.8	1.0	16.762	mg	
Material	2	Phos Bronze				1.0	12.12	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	11.47564	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.002424	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.001212	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	0.5454	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.001818	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.001212	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.01212	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.212E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.03636	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.01212	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.01212	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.001212	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.00606	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.01212	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	6.06E-5	mg	
Material	2	Nickel Plate				1.0	0.63	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	6.3E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00126	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.62811	mg	
Material	2	Gold Plate				1.0	0.25	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.24925	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	7.5E-4	mg	