



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2014-05-14	Contact Email	dave.benfer@te.com																													
Contact Phone Number		7179863725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1658622-8	Amount	4.876	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
EUREACH-0613	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Matte tin				1.0	0.0019504	g																										
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.0019504	g	N/A																									
Material	1	PLASTIC-2				1.0	1.080034	g																										
Substance	2	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	0.0540017	g	N/A																									
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.3240102	g	N/A																									
Substance	2	1,4-Benzenedicarb oxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	58.0	1.0	0.62641972	g	N/A																									
Substance	2	Carbon black	Supplier	1333-86-4	1.0	1.0	0.01080034	g	N/A																									
Substance	2	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	0.01080034	g	N/A																									
Substance	2	Antimony	Supplier	7440-36-0	5.0	1.0	0.0540017	g	N/A																									
Material	1	Nickel				1.0	0.0014628	g																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.0014628	g	N/A																									
Material	1	COPPER-2				1.0	0.8113664	g																										
Substance	2	Tin	Supplier	7440-31-5	9.0	1.0	0.07302298	g	N/A																									
Substance	2	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.00283978	g	N/A																									
Substance	2	Copper	Supplier	7440-50-8	90.65	1.0	0.73550364	g	N/A																									
Material	1	PLASTIC-1				1.0	2.9802112	g																										
Substance	2	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	0.14901056	g	N/A																									
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.89406336	g	N/A																									
Substance	2	1,4-Benzenedicarb oxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	59.0	1.0	1.75832461	g	N/A																									
Substance	2	Antimony	Supplier	7440-36-0	5.0	1.0	0.14901056	g	N/A																									
Substance	2	Carbon black	Supplier	1333-86-4	1.0	1.0	0.02980211	g	N/A																									
Material	1	Gold				1.0	9.752E-4	g																										
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	9.752E-4	g	N/A																									