



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2014-07-24	Contact Email	cc.wu@te.com				
Contact Phone Number	(86)21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-320568-1	Amount	2414.754	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	31113				1.0	1561.894	mg	
Material	2	Tin Plate				1.0	3.494	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	3.47653	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.013976	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.003494	mg	
Material	2	Copper				1.0	1558.4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.7792	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.5584	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.015584	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	1553.68584	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.015584	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.15584	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.15584	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.31168	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.5584	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.007792	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.15584	mg	
Sub-Item	1	21959-1				1.0	852.86	mg	
Material	2	PA66				1.0	176.4	mg	
Substance	3	Copper	Supplier	7440-50-8	0.02	1.0	0.03528	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	1.0	1.9404	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	98.78	1.0	174.24792	mg	
Substance	3	Bromine	Supplier	7726-95-6	0.1	1.0	0.1764	mg	
Material	2	Tin Plate				1.0	10.84	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	10.7858	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.04336	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.01084	mg	
Material	2	COLORANT				1.0	3.6	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	2.0	1.0	0.072	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	95.5	1.0	3.438	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	1.0	0.018	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	0.072	mg	
Material	2	Copper				1.0	662.02	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.33101	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.66202	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0066202	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	660.01739	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0066202	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.066202	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.066202	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.1324	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.66202	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0033101	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.066202	mg	