



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-01-15	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	205203-3	Amount	5460.19	Version	-	Identity																												
Manufacturer Item Name	CRIMP SNAP RCPT ASSY,SIZE 1	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	#1 SHELL/REAR/TN/ST/.120				1.0	1728.653	mg																										
Material	2	Carbon Steel				1.0	1633.8	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.30704	mg																										
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.32676	mg																										
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.32676	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.16338	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.32676	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	2.4507	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.6338	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.16338	mg																										
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	12.2535	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	6.5352	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	1.6338	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.016338	mg																										
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	1604.04033	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.8169	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.16338	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.008169	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.6338	mg																										
Material	2	Copper Plate				1.0	35.998	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.035998	mg																										
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	35.962	mg																										
Material	2	Tin Plate				1.0	58.855	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.23542	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	58.56072	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.058855	mg																										
Sub-Item	1	09 RCPT,INSERT,REAR				1.0	784.9	mg																										
Material	2	PA66-GF25				1.0	784.9	mg																										

Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	31.396	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	47.094	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	27.4715	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	482.7135	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	196.225	mg	
Sub-Item	1	09,RCPT,INSE RT,FRONT				1.0	1291.0	mg	
Material	2	PBT-GF30FR(17)				1.0	1291.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	387.3	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	426.03	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	12.91	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	12.91	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	64.55	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	387.3	mg	
Sub-Item	1	SZ1 SHELL/RCPT/FR/TN/ST/.120				1.0	1655.637	mg	
Material	2	Copper Plate				1.0	38.193	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.038193	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	38.15481	mg	
Material	2	Tin Plate				1.0	62.444	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.24978	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	62.13178	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.062444	mg	
Material	2	Carbon Steel				1.0	1555.0	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.05	1.0	0.7775	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1555	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.311	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	2.3325	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	1.555	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01555	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1555	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.555	mg	
Substance	3	Iron	Supplier	7439-89-6	97.9335	1.0	1522.86592	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	11.6625	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.035	1.0	0.54425	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	9.33	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.244	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.007775	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.555	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.7775	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1555	mg	