



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2013-12-28	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1658657-1	Amount	39114.42057	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	747536-3				1.0	6084.42769	mg	
Material	2	Tin Plate				1.0	156.7607	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.62704	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	155.9769	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.15676	mg	
Material	2	Copper Plate				1.0	110.36699	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.11037	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	110.25662	mg	
Material	2	Carbon Steel				1.0	1563.0	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.007815	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1563	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	9.378	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	2.0319	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	0.6252	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	2.3445	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01563	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.3126	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	1.563	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.563	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1563	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6785	1.0	1542.34496	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.563	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1563	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.7815	mg	
Material	2	Carbon Steel				1.0	2271.5	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.8172	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.4543	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.4543	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.22715	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.4543	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	3.40725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.2715	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.22715	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	17.03625	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	9.086	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	2.2715	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.022715	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	2230.12463	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.13575	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.22715	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0113575	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.2715	mg	
Material	2	PA66-GF25				1.0	1982.8	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	79.312	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	118.968	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	69.398	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	1219.422	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	495.7	mg	
Sub-Item	1	747534-2				1.0	3213.47129	mg	
Material	2	Tin Plate				1.0	90.43691	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.36175	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	89.98473	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.09043691	mg	
Material	2	Copper Plate				1.0	64.53438	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.06453438	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	64.46985	mg	
Material	2	Carbon Steel				1.0	3058.5	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0152925	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.30585	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	18.351	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	3.97605	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	1.2234	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.58775	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.030585	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.6117	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.0585	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.0585	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.30585	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6785	1.0	3018.08192	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.0585	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.30585	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.52925	mg	
Sub-Item	1	748627-2				2.0	5588.0	mg	
Material	2	Zinc Casting				2.0	5588.0	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.5588	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	2.0	2.794	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.05588	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	2.0	1.9558	mg	
Substance	3	Copper	Supplier	7440-50-8	3.0	2.0	167.64	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.05588	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0030	2.0	0.16764	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	2.794	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	5.588	mg	
Substance	3	Zinc	Supplier	7440-66-6	92.3105	2.0	5158.31074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.5588	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	2.0	240.284	mg	

Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	5.588	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	2.0	1.1176	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0040	2.0	0.22352	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.02794	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0050	2.0	0.2794	mg	
Sub-Item	1	747533-2				1.0	3171.32159	mg	
Material	2	Tin Plate				1.0	86.8481	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.34739	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	86.41386	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0868481	mg	
Material	2	Copper Plate				1.0	61.97349	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.06197349	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	61.91152	mg	
Material	2	Carbon Steel				1.0	3022.5	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0151125	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.30225	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	18.135	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	3.92925	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	1.209	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.53375	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.030225	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.6045	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.0225	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.0225	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.30225	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6785	1.0	2982.55766	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.0225	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.30225	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.51125	mg	
Sub-Item	1	747934-1				1.0	15469.2	mg	
Material	2	POLYVINYL CHLORIDE				1.0	15469.2	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	46.4076	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	1.8	1.0	278.4456	mg	
Substance	3	Barium	Supplier	7440-39-3	0.6	1.0	92.8152	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	4.34	1.0	671.36328	mg	
Substance	3	Hexanedioic acid, 1,6-bis(2-ethylhexyl) ester	Supplier	103-23-1	20.2	1.0	3124.7784	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	72.4	1.0	11199.7008	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diisodecyl ester	Phthalates (DINP, DIDP, DNOP)	26761-40-0	0.36	1.0	55.68912	mg	