



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A																									
<b>Supplier Information</b>																																		
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Engineer Product Compliance china																											
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2013-12-11	<b>Contact Email</b>	jrpenica@te.com																													
<b>Contact Phone Number</b>		717-592-3266																																
<b>Legal Statement</b>																																		
<b>Supplier Acceptance</b>	true																																	
<b>Legal Statement</b>																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
<b>Product</b>																																		
<b>Manufacturer Item number</b>	206061-1	<b>Amount</b>	9380.0	<b>Version</b>	-	<b>Identity</b>																												
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>																												
<b>Date</b>		<b>UOM</b>	Each																															
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true																																	
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
<b>Product Disclosure</b>																																		
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>																									
Sub-Item	1	1573524-4				1.0	9380.0	mg																										
Material	2	PA66-GF25				1.0	9380.0	mg																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	375.2	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	562.8	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	328.3	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	5768.7	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	2345.0	mg																										