



Form Type	Distribute	Version	2.0	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A		
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	-	Response Date	2013-03-08	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1734839-6	Amount	119.6	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	20.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	Phosphor Bronze		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	Tin (Sn)		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Housing				1.0	33.9	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	80.0	1.0	27.12	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	6.78	mg	
Material	1	Partition				1.0	36.1	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	16.245	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	55.0	1.0	19.855	mg	
Material	1	Latch				1.0	26.4	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.03	1.0	0.00792	mg	
Substance	2	Copper	Supplier	7440-50-8	94.47	1.0	24.94008	mg	
Substance	2	Tin	Supplier	7440-31-5	5.5	1.0	1.452	mg	
Material	1	Terminal				1.0	23.2	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.03	1.0	0.00696	mg	
Substance	2	Tin	Supplier	7440-31-5	5.5	1.0	1.276	mg	
Substance	2	Copper	Supplier	7440-50-8	94.47	1.0	21.91704	mg	