



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2015-02-19	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	206966-7	Amount	11785.5	Version	-	Identity			
Manufacturer Item Name	CABLE SHELL CLAMP SIZE 13	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	CABLE CLAMP SADDLE SZ 17				1.0	2697.0	mg	
Material	2	PA66-GF25				1.0	2697.0	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	107.88	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	161.82	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	94.395	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	1658.655	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	674.25	mg	
Sub-Item	1	SCREW, SELF-TAP, HI-LO TYPE, CROSS, PAN				2.0	1322.8	mg	
Material	2	Hi-Lo Tapping Screw				2.0	1309.572	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	2.0	1.96436	mg	
Substance	3	Iron	Supplier	7439-89-6	99.144	2.0	1298.36206	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.0030	2.0	0.03928716	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.7	2.0	9.167	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.0030	2.0	0.03928716	mg	
Material	2	Screw plating				2.0	13.228	mg	
Substance	3	Chromium	Supplier	7440-47-3	20.0	2.0	2.6456	mg	
Substance	3	Zinc	Supplier	7440-66-6	80.0	2.0	10.5824	mg	
Sub-Item	1	CABLE CLAMP BODY SIZE 13				1.0	6442.9	mg	
Material	2	(PA6+PA66)-GF20				1.0	6442.9	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	322.145	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.04	1.0	2.57716	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	128.858	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.32215	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	1224.151	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	22.0	1.0	1417.438	mg	
Substance	3	Polyamide Polymer Blend - ISO 1043-1 Term PA66+PA6	Supplier	1043-1-PA66+PA6	51.949	1.0	3347.02212	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0060	1.0	0.38657	mg	