



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2014-11-17	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-1761679-5	Amount	1949.414234	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	4-1364715-0				14.0	40.436731	mg	
Material	2	Nickel Plate				14.0	0.512188	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	14.0	0.00102438	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	14.0	5.1219E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	14.0	0.51065	mg	
Material	2	Tin Plate				14.0	0.260843	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	14.0	2.6058E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	14.0	0.26058	mg	
Material	2	Phos Bronze				14.0	39.5	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	14.0	3.95E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	14.0	0.005925	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	14.0	0.0079	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	14.0	0.13825	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	14.0	0.00395	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	14.0	2.291	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	14.0	0.0395	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	14.0	0.1185	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	14.0	0.00395	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	14.0	36.78773	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	14.0	0.0395	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	14.0	0.0395	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	14.0	0.00395	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	14.0	1.975E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	14.0	0.01975	mg	
Material	2	Gold Plate				14.0	0.0862	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	14.0	0.0859414	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	14.0	2.586E-4	mg	
Material	2	Gold Plate				14.0	0.0775	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	14.0	2.325E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	14.0	0.0772675	mg	
Sub-Item	1	1364809-7				1.0	1383.3	mg	
Material	2	PBT-GF30-FR(17)				1.0	1383.3	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	705.483	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	110.664	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	401.157	mg	
Substance	3	Antimony oxide (Sb ₂ O ₃)	Supplier	1309-64-4	4.0	1.0	55.332	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	110.664	mg	