



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2014-03-03	Contact Email	dave.benfer@te.com				
Contact Phone Number	7179863725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-5174341-5	Amount	16.49573806	Version	-	Identity			
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	173272-7				1.0	0.525	g	
Material	2	PBT-GF15				1.0	0.525	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.5	1.0	0.002625	g	
Substance	3	Poly(butylene terephthalate) - ISO 1043-1 Term PBT	Supplier	1043-1-PBT	61.0	1.0	0.32025	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	0.042	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	15.0	1.0	0.07875	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	15.0	1.0	0.07875	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.5	1.0	0.002625	g	
Sub-Item	1	174227-5				1.0	0.78	g	
Material	2	PBT-GF30				1.0	0.78	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.234	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	0.0546	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.5	1.0	0.0039	g	
Substance	3	Poly(butylene terephthalate) - ISO 1043-1 Term PBT	Supplier	1043-1-PBT	42.0	1.0	0.3276	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	5.5	1.0	0.0429	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	15.0	1.0	0.117	g	
Sub-Item	1	4-173643-4				34.0	0.04020035	g	
Material	2	Nickel Plate				34.0	0.001418	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	34.0	2.836E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	1.418E-6	g	

Substance	3	Nickel	Nickel	7440-02-0	99.7	34.0	0.00141375	g	
Material	2	Gold Plate				34.0	2.60799E-5	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	34.0	2.600166E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	34.0	7.82397E-8	g	
Material	2	Tin Plate				34.0	1.5597E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	34.0	1.55815E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.9001	34.0	1.5582E-4	g	
Material	2	Phos Bronze				34.0	0.0386003	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	34.0	1.930015E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	3.86003E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	34.0	5.790045E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	34.0	3.86003E-6	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	34.0	7.72006E-6	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	34.0	3.86003E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.12	34.0	4.632036E-5	g	
Substance	3	Copper	Supplier	7440-50-8	97.2735	34.0	0.03754786	g	
Substance	3	Tin	Supplier	7440-31-5	2.2	34.0	8.4921E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	34.0	3.86003E-5	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	34.0	1.544012E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	34.0	3.86003E-6	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	34.0	3.86003E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	34.0	3.86003E-5	g	
Sub-Item	1	1-174669-2				2.0	6.40889597	g	
Material	2	Nickel Plate				2.0	0.00104	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	2.08E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	1.04E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.00103688	g	
Material	2	Brass				2.0	6.4077	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	6.4077E-5	g	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	1.79559773	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.00320385	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	6.4077E-4	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.00320385	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.0064077	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	4.5815055	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	6.4077E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	6.4077E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	3.20385E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.0128154	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	3.2039E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.00320385	g	
Material	2	Tin Plate				2.0	1.5597E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	2.0	1.55815E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.9001	2.0	1.5582E-4	g	
Sub-Item	1	4-173643-3				34.0	0.02959218	g	
Material	2	Nickel Plate				34.0	0.00104	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	34.0	2.08E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	1.04E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	34.0	0.00103688	g	
Material	2	Gold Plate				34.0	2.60799E-5	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	34.0	2.600166E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	34.0	7.82397E-8	g	
Material	2	Tin Plate				34.0	1.5021E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	34.0	1.0E-8	g	

Substance	3	Tin	Supplier	7440-31-5	99.9001	34.0	1.500599E-6	g	
Material	2	Phos Bronze				34.0	0.0285246	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	34.0	1.42623E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	2.85246E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	34.0	4.27869E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	34.0	2.85246E-6	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	34.0	5.70492E-6	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	34.0	2.85246E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.12	34.0	3.422952E-5	g	
Substance	3	Copper	Supplier	7440-50-8	97.2735	34.0	0.02774688	g	
Substance	3	Tin	Supplier	7440-31-5	2.2	34.0	6.2754E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	34.0	2.85246E-5	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	34.0	1.140984E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	34.0	2.85246E-6	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	34.0	2.85246E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	34.0	2.85246E-5	g	