



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer		
Company Unique ID	485203835	Response Date	2014-06-17	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	226990-1	Amount	9621.920895	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	9-226984-2				1.0	77.234927	mg	
Material	2	Tin Plate				1.0	1.626249	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00162462	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	1.62462	mg	
Material	2	Nickel Plate				1.0	0.850678	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00170136	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	8.5068E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.84813	mg	
Material	2	Brass Wire				1.0	74.758	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0523306	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	53.45197	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	7.4758E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	1.0	20.93037	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.037379	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	7.4758E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.037379	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.074758	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0074758	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0074758	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0074758	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.7379E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.14952	mg	
Sub-Item	1	222500-1				1.0	363.2269	mg	
Material	2	PMP				1.0	363.2269	mg	
Substance	3	1-Octadecene, polymer with 1-hexadecene and 4-methyl-1-pentene	Supplier	81229-87-0	99.0	1.0	359.59463	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	3.63227	mg	
Sub-Item	1	9-228567-0				1.0	206.287668	mg	
Material	2	Phos Bronze				1.0	199.7	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	189.08295	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.03994	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.01997	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	8.9865	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.029955	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.01997	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.1997	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.001997	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.5991	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.1997	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.1997	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.01997	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.09985	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.1997	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.985E-4	mg	
Material	2	Tin Plate				1.0	2.39678	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00239438	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	2.39439	mg	
Material	2	Nickel Plate				1.0	4.190888	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00838178	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00419089	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	4.17832	mg	
Sub-Item	1	415142-1				1.0	2746.3	mg	
Material	2	PBT-GF15				1.0	2746.3	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	24.7167	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.5	1.0	68.6575	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	137.315	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	2.7463	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	8.2389	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	13.7315	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	10.9852	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	57.8	1.0	1587.3614	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[1-oxooctadecyl]oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	13.7315	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	466.871	mg	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	15.0	1.0	411.945	mg	
Sub-Item	1	9-226986-0				1.0	6228.8714	mg	
Material	2	Tri Chrome Film				1.0	0.2264	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	1.0	0.06792	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	0.02264	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	1.0	0.13584	mg	
Material	2	Copper Plate				1.0	73.045	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.073045	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	72.97195	mg	
Material	2	Nickel Plate				1.0	54.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.1092	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0546	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	54.4362	mg	
Material	2	Zinc Alloy				1.0	6101.0	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	1.0	2.13535	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	1.0	1.2202	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0030	1.0	0.18303	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.06	1.0	3.6606	mg	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	15.2525	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.6101	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.0315	1.0	5797.87181	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	262.343	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.6101	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.06101	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	6.101	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	6.101	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	1.0	3.0505	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	1.2202	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0050	1.0	0.30505	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.030505	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0040	1.0	0.24404	mg	