



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	DONNIY LIM	Contact Title	Global Account Manager		
Company Unique ID	-	Response Date	2014-07-04	Contact Email	donna.lim@te.com				
Contact Phone Number	+60-4-8102110								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	292250-3	Amount	332.2	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	6-292121-2				3.0	27.4	mg	
Material	2	Nickel Plate				3.0	0.38	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	7.6E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	3.8E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.37886	mg	
Material	2	Tin Plate				3.0	0.22	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	3.0	8.8E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	3.0	0.2189	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	2.2E-4	mg	
Material	2	Brass				3.0	26.8	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	1.34E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.0536	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00268	mg	
Substance	3	Copper	Supplier	7440-50-8	68.5	3.0	18.358	mg	
Substance	3	Zinc	Supplier	7440-66-6	30.9475	3.0	8.29393	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.0268	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	2.68E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00268	mg	
Substance	3	Iron	Supplier	7439-89-6	0.07	3.0	0.01876	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	2.68E-4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.0134	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.00268	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	0.0268	mg	
Sub-Item	1	175488-3				1.0	250.0	mg	
Material	2	POLYAMIDE 66				1.0	250.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	7.5	mg	
Substance	3	Phosphoric acid, trimethyl ester	Supplier	512-56-1	0.05	1.0	0.125	mg	

Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	86.95	1.0	217.375	mg	
Substance	3	Nitrogen compounds - ISO 1043-4 code #FR(30)	Supplier	1043-4-FR30	10.0	1.0	25.0	mg	