



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-01-20	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-767004-2	Amount	1269.9622	Version	-	Identity			
Manufacturer Item Name	MICT,RECPT,038,ASSY.,025,RE C	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	38 POS. MICTOR RECEPTACLE HOUS				1.0	916.0	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	916.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	27.48	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	613.72	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	274.8	mg	
Sub-Item	1	MICTOR STD RECPT CONTACT,PL TD,				38.0	7.735	mg	
Material	2	Tin-Lead Plate				38.0	0.075	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	40.0	38.0	0.03	mg	
Substance	3	Tin	Supplier	7440-31-5	60.0	38.0	0.045	mg	
Material	2	Copper Alloy				38.0	7.21	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	38.0	0.003605	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	38.0	0.0721	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	38.0	0.08652	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	38.0	0.00721	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7635	38.0	6.68825	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	38.0	0.004326	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	38.0	7.21E-5	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	38.0	0.02163	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	38.0	0.00721	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	38.0	0.01442	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	38.0	7.21E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	38.0	7.21E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	38.0	0.30282	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	38.0	3.605E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	38.0	3.605E-5	mg	

Material	2	Gold Plate				38.0	0.065	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	38.0	0.064805	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	38.0	1.95E-4	mg	
Material	2	Nickel Plate				38.0	0.385	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	38.0	7.7E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	38.0	3.85E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	38.0	0.38385	mg	
Sub-Item	1	MICTOR,REC PT,BUS,.062,REC,PLT				1.0	60.0322	mg	
Material	2	Tin-Lead Plate				1.0	0.88	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	40.0	1.0	0.352	mg	
Substance	3	Tin	Supplier	7440-31-5	60.0	1.0	0.528	mg	
Material	2	Phos Bronze				1.0	56.58	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	53.57192	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.011316	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.005658	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	2.5461	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.008487	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.005658	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.05658	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.658E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.16974	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.05658	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.05658	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.005658	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.02829	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.05658	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.829E-4	mg	
Material	2	Gold Plate				1.0	0.0292	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.0291124	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	8.76E-5	mg	
Material	2	Nickel Plate				1.0	2.543	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.005086	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.002543	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.53537	mg	