



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER																											
Company Unique ID	485203835	Response Date	2014-02-03	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	205206-3	Amount	6611.45302	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	205230-2				1.0	1029.0	mg																										
Material	2	PA66-GF25				1.0	1029.0	mg																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	41.16	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	61.74	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	36.015	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanedyl)imino-1,6-hexanedyl]	Supplier	32131-17-2	61.5	1.0	632.835	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	257.25	mg																										
Sub-Item	1	1-745118-9				1.0	2397.89302	mg																										
Material	2	Copper Plate				1.0	47.14962	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04714962	mg																										
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	47.10247	mg																										
Material	2	Carbon Steel				1.0	2271.5	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.8172	mg																										
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.4543	mg																										
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.4543	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.22715	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.4543	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	3.40725	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.2715	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.22715	mg																										
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	17.03625	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	9.086	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	2.2715	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.022715	mg																										
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	2230.12463	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.13575	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.22715	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0113575	mg																										

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.2715	mg	
Material	2	Tin Plate				1.0	79.2434	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.31697	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	78.84718	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0792434	mg	
Sub-Item	1	1-204552-7				1.0	2230.76	mg	
Material	2	Copper Plate				1.0	43.95	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04395	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	43.90605	mg	
Material	2	Carbon Steel				1.0	2115.04	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.05	1.0	1.05752	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.2115	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.42301	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	3.17256	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	2.11504	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0211504	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.2115	mg	
Substance	3	Iron	Supplier	7439-89-6	97.9335	1.0	2071.3327	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.11504	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	15.8628	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.035	1.0	0.74026	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	12.69024	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.69203	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0105752	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.11504	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.05752	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.2115	mg	
Material	2	Tin Plate				1.0	71.77	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.28708	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	71.41115	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.07177	mg	
Sub-Item	1	205229-2				1.0	953.8	mg	
Material	2	PA66-GF25				1.0	953.8	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	38.152	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	57.228	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	33.383	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	586.587	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	238.45	mg	