



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	485203835	Response Date	2014-04-04	Contact Email	cc.wu@tycoelectronics.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	3-640440-4	Amount	692.508	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	640538-4				1.0	319.7	mg																										
Material	2	COLORANT				1.0	6.394	mg																										
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	14.76	1.0	0.94375	mg																										
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	0.06394	mg																										
Substance	3	Poly[imino(1-oxo-1,6-hexanediyl)]	Supplier	25038-54-4	84.24	1.0	5.38631	mg																										
Material	2	PA66				1.0	313.306	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	99.0	1.0	310.17294	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	3.13306	mg																										
Sub-Item	1	640437-5				4.0	93.202	mg																										
Material	2	Tin Plate				4.0	2.221	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	4.0	0.00221878	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	4.0	2.21878	mg																										
Material	2	Nickel Plate				4.0	0.581	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	4.0	0.001162	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	5.81E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.57926	mg																										
Material	2	Phos Bronze				4.0	90.4	mg																										
Substance	3	Copper	Supplier	7440-50-8	93.1335	4.0	84.19268	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.01808	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	0.2712	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	0.00904	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	4.0	0.3164	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	4.0	0.01356	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.0904	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	9.04E-4	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.0904	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.00904	mg																										
Substance	3	Tin	Supplier	7440-31-5	5.8	4.0	5.2432	mg																										

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	4.52E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	4.0	0.00904	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.0452	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.0904	mg	