



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	485203835	Response Date	2013-08-27	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	205210-3	Amount	13457.331	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	205238-2				1.0	2372.4	mg																										
Material	2	PA66-GF25				1.0	2372.4	mg																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	94.896	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	142.344	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	83.034	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1459.026	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	593.1	mg																										
Sub-Item	1	205237-2				1.0	2172.0	mg																										
Material	2	PA66-GF25				1.0	2172.0	mg																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	86.88	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	130.32	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	76.02	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1335.78	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	543.0	mg																										
Sub-Item	1	1-204570-7				1.0	3512.06	mg																										
Material	2	Carbon Steel				1.0	3317.5	mg																										
Substance	3	Carbon	Supplier	7440-44-0	0.05	1.0	1.65875	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.33175	mg																										
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.6635	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.97625	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.3175	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.033175	mg																										

Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.33175	mg	
Substance	3	Iron	Supplier	7439-89-6	97.9335	1.0	3248.94386	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.3175	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	24.88125	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.035	1.0	1.16113	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	19.905	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	2.654	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0165875	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.3175	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.65875	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.33175	mg	
Material	2	Tin Plate				1.0	120.67	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.48268	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	120.06665	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.12067	mg	
Material	2	Copper Plate				1.0	73.89	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.07389	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	73.81611	mg	
Sub-Item	1	1-745120-5				1.0	5400.871	mg	
Material	2	Carbon Steel				1.0	5189.3	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.05	1.0	2.59465	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.51893	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	1.03786	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	7.78395	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	5.1893	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.051893	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.51893	mg	
Substance	3	Iron	Supplier	7439-89-6	97.9335	1.0	5082.06312	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	5.1893	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	38.91975	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.035	1.0	1.81626	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	31.1358	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	4.15144	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0259465	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	5.1893	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	2.59465	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.51893	mg	
Material	2	Tin Plate				1.0	131.277	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.52511	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	130.62062	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.13128	mg	
Material	2	Copper Plate				1.0	80.294	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.080294	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	80.21371	mg	