



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2014-10-28	Contact Email	cc.wu@te.com				
Contact Phone Number	+86-21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	3-640440-5	Amount	926.01	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	640537-5				1.0	460.0	mg	
Material	2	PA66				1.0	450.8	mg	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]]	Supplier	32131-17-2	99.0	1.0	446.292	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	4.508	mg	
Material	2	COLORANT				1.0	9.2	mg	
Substance	3	14H-Benz[4,5]isoquin[2,1-a]perimidin-14-one	Supplier	6829-22-7	5.72	1.0	0.52624	mg	
Substance	3	Poly[[imino(1-oxo-1,6-hexanediy)]]	Supplier	25038-54-4	93.71	1.0	8.62132	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.57	1.0	0.05244	mg	
Sub-Item	1	640437-5				5.0	93.202	mg	
Material	2	Nickel Plate				5.0	0.581	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	5.0	0.001162	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	5.81E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	5.0	0.57926	mg	
Material	2	Phos Bronze				5.0	90.4	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	5.0	84.19268	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	5.0	0.01808	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	5.0	0.2712	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	5.0	0.00904	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	5.0	0.3164	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	5.0	0.01356	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	5.0	0.0904	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	5.0	9.04E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.0904	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.00904	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	5.0	5.2432	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	4.52E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.00904	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	5.0	0.0452	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	5.0	0.0904	mg	
Material	2	Tin Plate				5.0	2.221	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	5.0	0.00221878	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	5.0	2.21878	mg	