



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A		
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	-	Response Date	2013-07-10	Contact Email	cc.wu@te.com				
Contact Phone Number	(86)21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	3-641208-3	Amount	1120.9655	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	6-647656-2				3.0	192.6885	mg	
Material	2	Tin Plate				3.0	0.673	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	3.0	6.7233E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	3.0	0.67233	mg	
Material	2	Brass				3.0	191.105	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	136.64007	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	0.00191105	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	3.0	53.50462	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.0955525	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	0.00191105	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.0955525	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.1911	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.0191105	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.0191105	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	0.13377	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.0191105	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	9.5553E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.38221	mg	
Material	2	Gold Plate				3.0	0.0565	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	3.0	0.055935	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	3.0	5.65E-4	mg	
Material	2	Nickel Plate				3.0	0.854	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	3.0	0.001708	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	8.54E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.85144	mg	
Sub-Item	1	Polyester Resin				1.0	542.9	mg	
Material	2	PBT-GF7				1.0	542.9	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-	Supplier	80-05-7	0.01	1.0	0.05429	mg	

Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	35.2885	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	162.87	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	43.432	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	5.429	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	295.82621	mg	