



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Manager Environmental Engineering		
Company Unique ID	485203835	Response Date	2014-05-05	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	213904-1	Amount	12534.670105	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	213903-1				1.0	7192.070105	mg	
Material	2	(PA6+PA66)-GF20				1.0	7192.070105	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	359.60351	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.04	1.0	2.87683	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	143.8414	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.3596	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	1366.49332	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	22.0	1.0	1582.25542	mg	
Substance	3	Polyamide Polymer Blend - ISO 1043-1 Term PA66+PA6	Supplier	1043-1-PA66+PA6	51.949	1.0	3736.2085	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0060	1.0	0.43152	mg	
Sub-Item	1	5019024-2				2.0	1322.8	mg	
Material	2	Hi-Lo Tapping Screw				2.0	1309.572	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	2.0	1.96436	mg	
Substance	3	Iron	Supplier	7439-89-6	99.144	2.0	1298.36206	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.0030	2.0	0.03928716	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.7	2.0	9.167	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.0030	2.0	0.03928716	mg	
Material	2	Screw plating				2.0	13.228	mg	
Substance	3	Chromium	Supplier	7440-47-3	20.0	2.0	2.6456	mg	
Substance	3	Zinc	Supplier	7440-66-6	80.0	2.0	10.5824	mg	
Sub-Item	1	207681-1				1.0	2697.0	mg	
Material	2	PA66-GF25				1.0	2697.0	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	107.88	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	161.82	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	94.395	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1658.655	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	674.25	mg	