



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Mgr Environmental Engineering		
Company Unique ID	-	Response Date	2014-07-14	Contact Email	jrpenica@te.com				
Contact Phone Number	1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	33462	Amount	4770.548594	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	Cu Alloy		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	Tin		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Copper				1.0	4745.1	mg	
Substance	2	Copper	Supplier	7440-50-8	99.7525	1.0	4733.35588	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.47451	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.047451	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.47451	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.047451	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.94902	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	4.7451	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.37255	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	2.37255	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.23726	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0237255	mg	
Material	1	Tin Plate				1.0	13.278	mg	
Substance	2	Tin	Supplier	7440-31-5	99.5	1.0	13.21161	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.053112	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.013278	mg	
Material	1	Brazing Filler				1.0	12.170594	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	6.7	1.0	0.81543	mg	
Substance	2	Copper	Supplier	7440-50-8	87.05	1.0	10.5945	mg	
Substance	2	Silver	Supplier	7440-22-4	6.25	1.0	0.76066	mg	