

Form Type	Distribute	Version	rsion 2.0		Ref		IPC 175	2A	Sectional	s	Manufacturi Info/ Materia Info		Subsectionals	D, A
	,	-			S	upplier I	nformati	on						
Company Name	TE Connectiv	ity Request Document I	D			Contact	Name	Penica	a, John R	Con	tact Title	Mg	r Environmental	Engineering
Company Unique ID	-		Response Date		2014-06-23		Contact Email		jrpenica@te.com			<u> </u>		
Contact Phone	umber 17175923266							1						
		1				Legal S	tatement							
Supplier Acceptance	true													
Legal Statemen	t													
The information plus in the contract that the contract the contract that the contract the contra	provided in this on the new purchase sp	document is base ecifications or exi	d upo sting	n reasonab contractual	ole inqui or othe	ry of our : r agreem	suppliers. ents term	This inf s betwe	ormation is en TE Coni	subje nectiv	ect to change. ity (or its affili	. Thi ated	s information doe l companies) and	es not in any its custome
	1	1					duct	1						
Manufacturer Item number	280363	Amount		1177.839		Version		-	lder		tity			
Manufacturer Item Name		Weight Uon	n	mg		Mfr Site			Authority		nority			
Date		UOM		Each										
EURoHS-0508	Product(s) me	ets EU RoHS red	quirem	ent withou	t any ex	emptions	- true							
ChinaRoHS- 0508	Product(s) is e	eligible for markin e	g with	the e code	under (	China's N	/leasures	for Adm	inistration o	of the	control of poll	lutio	n by Electronic In	formation
EUREACH-0613		es not contain RE	ACH	Substance	s Of Ver	y High C	oncern al	oove the	limits per t	he de	finition within	RE	ACH - true	
	, ,	i					ng Inform		•					
J-STD-020 MSL Rating		Max Total a Wave Time				Ramp Rate			Wav Add		re itional Info			
Classification Temp		Max Wave Solder Time	<u> </u>	0.0		Ramp Down Rate				Psl Rating Reflow				
Max Time Within 5		Psl Rating Wave				Package Designator			Size		1	0.0		
Time Above 217	,	Reflow Additional I	nfo			Preheat Max Temp			Tern Allo		ninal Base NA		C	
Preheat Duration		bulk Solder Termination		NAC		Nbr or Reflow Cycles			Termi Platin			NAC		
Preheat Min Temp		Nbr of Instances		0		Component Temp Spike			Sha				.C	
	•	•			F	roduct I	Disclosu	re						
Sub- Item/Material/ Substance	Level	Name		stance gory	Substance CAS		Substar Concen		Quantity	Mass per U		nit	иом	Exemption
Sub-Item	1	Pheylene Oxide Compound							1.0		1177.839		mg	
Material	2	PPE+PS					-		1.0		1177.839		mg	
Substance	3	Phenol, 2,6- dimethyl-,	Supplier		25134-01-4		46.2	1.0		544.16162			mg	
Substance	3	homopolymer  Benzene, ethenyl-, polymer with	Supplier		9003-55-8		40.0		1.0		471.1356		mg	
Substance	3	1,3-butadiene Phosphoric acid, triphenyl ester	Supplier		115-86-6		1.0		1.0		11.77839		mg	
Substance	3	Phosphoric acid, P,P-1,3- phenylene P,P,P,- tetraphenyl ester	Supp	Supplier		57583-54-7		8.0			94.22712		mg	
Substance	3	Magnesium oxide (MgO)	Supp	Supplier		1309-48-4			1.0		3.53352		mg	
Substance	3	Benzene, methyl-	Supplier		108-88-3		0.1		1.0		1.17784		mg	
Substance	3	Phosphorous acid, triisodecyl ester	Supp	Supplier		25448-25-3			1.0		11.77839		mg	
Substance	3	Carbon black	Supp	Supplier		1333-86-4		0.1		1.0			mg	
Substance	3	Zinc sulfide (ZnS)	Supp	Supplier		1314-98-3			1.0		3.53352		mg	
Substance	3	1-Butene, polymer with ethene	Supp	upplier 29		-34-7	3.0		1.0		35.33517		mg	