



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A							
Supplier Information														
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER							
Company Unique ID	-	Response Date	2013-05-02	Contact Email	cc.wu@te.com									
Contact Phone Number	(86)21-33259321													
Legal Statement														
Supplier Acceptance	true													
Legal Statement														
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.														
Product														
Manufacturer Item number	33471	Amount	8593.131404	Version	-	Identity								
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority								
Date		UOM	Each											
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions													
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products													
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH													
Product Disclosure														
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption					
Material	1	Copper				1.0	8491.249728	mg						
Substance	2	Copper	Supplier	7440-50-8	99.6975	1.0	8465.5637	mg						
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.84912	mg						
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0849125	mg						
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.84912	mg						
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0849125	mg						
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	1.69825	mg						
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	8.49125	mg						
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	8.49125	mg						
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	4.24562	mg						
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.84912	mg						
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.04245625	mg						
Material	1	Tin Plate				1.0	56.971676	mg						
Substance	2	Tin	Supplier	7440-31-5	99.5	1.0	56.68682	mg						
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.22789	mg						
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.05697168	mg						
Material	1	Brazing Filler				1.0	44.91	mg						
Substance	2	Phosphorus	Supplier	7723-14-0	6.7	1.0	3.00897	mg						
Substance	2	Copper	Supplier	7440-50-8	87.05	1.0	39.09416	mg						
Substance	2	Silver	Supplier	7440-22-4	6.25	1.0	2.80688	mg						