



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	485203835	Response Date	2014-07-31	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	34124	Amount	1142.931	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Copper				1.0	1131.112	mg																										
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	0.56556	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.13111	mg																										
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01131112	mg																										
Substance	2	Copper	Supplier	7440-50-8	99.6975	1.0	1127.69039	mg																										
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01131112	mg																										
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.11311	mg																										
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.11311	mg																										
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.22622	mg																										
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	1.13111	mg																										
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00565556	mg																										
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.11311	mg																										
Material	1	Tin Plate				1.0	7.919	mg																										
Substance	2	Tin	Supplier	7440-31-5	99.5	1.0	7.8794	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.031676	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.007919	mg																										
Material	1	Brazing Filler				1.0	3.9	mg																										
Substance	2	Phosphorus	Supplier	7723-14-0	6.7	1.0	0.2613	mg																										
Substance	2	Copper	Supplier	7440-50-8	87.05	1.0	3.39495	mg																										
Substance	2	Silver	Supplier	7440-22-4	6.25	1.0	0.24375	mg																										