



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A		
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	PROD COMPLIANCE ENGINEER		
<b>Company Unique ID</b>	-	<b>Response Date</b>	2013-07-02	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	(86)21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	3-350819-2	<b>Amount</b>	951.74	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>REACH-0209</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	520949-2				1.0	629.14	mg	
Material	2	Tin Plate				1.0	19.82	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	19.7209	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.07928	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.01982	mg	
Material	2	Brass				1.0	609.32	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0060932	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0175	1.0	170.71623	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.30466	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.060932	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.30466	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.60932	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	435.6638	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0060932	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.060932	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0030466	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.21864	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.060932	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.30466	mg	
Sub-Item	1	350860-3				1.0	322.6	mg	
Material	2	COLORANT				1.0	0.7985	mg	
Substance	3	C.I. Pigment Blue 29	Supplier	57455-37-5	1.83	1.0	0.01461255	mg	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]]	Supplier	32131-17-2	97.69	1.0	0.78005	mg	
Substance	3	C.I. Pigment Blue 36	Supplier	68187-11-1	0.48	1.0	0.0038328	mg	
Material	2	COLORANT				1.0	3.2	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	5.95	1.0	0.1904	mg	

Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	94.05	1.0	3.0096	mg	
Material	2	PA66				1.0	318.6015	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.5	1.0	1.59301	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	99.5	1.0	317.00849	mg	