



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																	
Supplier Information																										
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer																			
Company Unique ID	485203835	Response Date	2014-07-22	Contact Email	cc.wu@te.com																					
Contact Phone Number	+86-21-33259321																									
Legal Statement																										
Supplier Acceptance	true																									
Legal Statement																										
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																										
Product																										
Manufacturer Item number	350792-1	Amount	2698.578	Version	-	Identity																				
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																				
Date		UOM	Each																							
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																									
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																									
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed																									
Product Disclosure																										
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																	
Sub-Item	1	350791-1				1.0	1898.294	mg																		
Material	2	PA				1.0	1898.294	mg																		
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	6.19224	mg																		
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	8.80239	mg																		
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.00569488	mg																		
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]]	Supplier	32131-17-2	0.9451	1.0	17.94078	mg																		
Substance	3	Benzenepropamide, N,N-1,6-hexanediy]bis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	7.60077	mg																		
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.0626437	mg																		
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	0.47457	mg																		
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	3.81937	mg																		
Substance	3	Octadecanamide, N,N-1,2-ethanediy]bis-	Supplier	110-30-5	0.1901	1.0	3.60866	mg																		
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	172.20754	mg																		
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	1677.57936	mg																		
Sub-Item	1	770528-1				4.0	200.071	mg																		
Material	2	Tin Plate				4.0	5.071	mg																		
Substance	3	Tin	Supplier	7440-31-5	97.85	4.0	4.96197	mg																		

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.2	4.0	0.010142	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	4.0	0.076065	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.35	4.0	0.0177485	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	0.005071	mg	
Material	2	Phos Bronze				4.0	195.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	4.0	184.63282	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.039	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	0.0195	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	4.0	8.775	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	4.0	0.02925	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.0195	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.195	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	0.00195	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	0.585	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	4.0	0.195	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.195	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	4.0	0.0195	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.0975	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.195	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	9.75E-4	mg	