



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	M. Global Product Compliance																											
Company Unique ID	485203835	Response Date	2014-06-27	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5-103958-9	Amount	1623.18226	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	5-103624-8				10.0	87.155226	mg																										
Material	2	Phos Bronze				10.0	83.9	mg																										
Substance	3	Copper	Supplier	7440-50-8	94.6835	10.0	79.43946	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.01678	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.00839	mg																										
Substance	3	Tin	Supplier	7440-31-5	4.5	10.0	3.7755	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	10.0	0.012585	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.00839	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.0839	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	8.39E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.2517	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	10.0	0.0839	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.0839	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.00839	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.04195	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.0839	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	4.195E-4	mg																										
Material	2	Nickel Plate				10.0	1.6	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	0.0032	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	0.0016	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	1.5952	mg																										
Material	2	Tin Plate				10.0	1.525226	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	0.0015237	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	1.5237	mg																										
Material	2	Gold Plate				10.0	0.13	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.12961	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	3.9E-4	mg																										
Sub-Item	1	104257-9				1.0	751.63	mg																										
Material	2	PBT-GF15				1.0	751.63	mg																										
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	11.27445	mg																										

Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	3.75815	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	3.00652	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.9	1.0	420.16117	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	37.5815	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	3.0	1.0	22.5489	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	6.76467	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[[1-oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	3.75815	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	127.7771	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	2.25489	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	15.0	1.0	112.7445	mg	