



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	-	Response Date	2013-08-15	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-104068-6	Amount	2866.7965	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	5-103917-2				60.0	12.26487	mg	
Material	2	Phos Bronze				60.0	11.7933	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	60.0	11.16631	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	60.0	0.00235866	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	60.0	0.00117933	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	60.0	0.5307	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	60.0	0.00176899	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	60.0	0.0117933	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	60.0	0.00117933	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	60.0	1.1793E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	60.0	0.0353799	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	60.0	0.0117933	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	60.0	0.0117933	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	60.0	0.00117933	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	60.0	0.00589665	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	60.0	0.0117933	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	60.0	5.89665E-5	mg	
Material	2	Tin Plate				60.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	60.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	60.0	0.07452547	mg	
Material	2	Gold Plate				60.0	0.1721	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	60.0	0.17158	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	60.0	5.163E-4	mg	
Material	2	Nickel Plate				60.0	0.219	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	60.0	4.38E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	60.0	2.19E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	60.0	0.21834	mg	
Material	2	Gold Plate				60.0	0.00587	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	60.0	0.00585239	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	60.0	1.761E-5	mg	

Sub-Item	1	2-104034-7				1.0	2130.9043	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	2130.9043	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 0909	3.0	1.0	63.92713	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	1427.70588	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	639.27129	mg	