



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2014-11-25	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	31890	<b>Amount</b>	914.541425	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>EUREACH-1213</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	30692				1.0	624.967375	mg	
Material	2	Tin Plate				1.0	5.957375	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	5.92759	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.0238295	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00595737	mg	
Material	2	Copper				1.0	619.01	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.30951	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.61901	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0061901	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	617.13749	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0061901	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.061901	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.061901	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.1238	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.61901	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00309505	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.061901	mg	
Sub-Item	1	21957-1				1.0	289.57405	mg	
Material	2	Tin Plate				1.0	4.23	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	4.20885	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.01692	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00423	mg	
Material	2	Copper				1.0	207.44	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.10372	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.20744	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0020744	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	206.81249	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0020744	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.020744	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.020744	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.041488	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.20744	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0010372	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.020744	mg	
Material	2	PA66				1.0	76.345969	mg	
Substance	3	Copper	Supplier	7440-50-8	0.02	1.0	0.01526919	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	1.0	0.83981	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	98.78	1.0	75.41455	mg	
Substance	3	Bromine	Supplier	7726-95-6	0.1	1.0	0.07634597	mg	
Material	2	COLORANT				1.0	1.558081	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.58	1.0	0.00903687	mg	
Substance	3	9,10-Anthracenedione, 1-(methylamino)-	Supplier	82-38-2	2.7	1.0	0.04206819	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	96.38	1.0	1.50168	mg	
Substance	3	3H-Naphtho[1,2,3-de]quinoline-2,7-dione, 3-methyl-6-[(4-methylphenyl)amino]-	Supplier	81-39-0	0.34	1.0	0.00529747	mg	